
Project	Catalog #	Туре
Prepared by	Notes	Date



## HC8 | HM8 | 81

8-inch LED downlight and wall wash

### Typical Applications

 $Office \boldsymbol{\cdot} Education \boldsymbol{\cdot} Healthcare \boldsymbol{\cdot} Hospitality$ 

## 🖌 Interactive Menu

- Order Information page 2
- Product Specifications page 4
- Photometric Data page 5
- Energy & Performance Data page 8
- Connected Systems page 10
- Product Warranty

## Product Certification



## **Product Features**


10

## **Control Compatibility**

|--|--|--|

### **Top Product Features**

- New construction/remodel series; 500 to 8,000 lumens
- Mounting frame converts to remodel that installs from below the ceiling
- 2700K, 3000K, 3500K, 4000K, 5000K CCT; 80 or 90 CRI
- Reflector distributions in Narrow, Medium, Wide, and Wall Wash with rotatable linear spread lens
- Reflector finishes in Specular clear, semi-specular (haze), matte white, black baffle, and white baffle finishes
- Quick Spec emergency backup mounting frames fast delivery option





## HC8 | HM8 | 81

### **Mounting Frame Order Information**

Sample Number: HC820D010REM7 - HM80520835 - 81MDC

A complete luminaire consists of a mounting frame, LED module, and reflector; ordered separately

Mounting Frame	Lumens	Driver Options	Factory Installed Emergency & Connected Lighting Options	Accessories (Order & Install Separately)
HC8 = 8" new construction downlight housing HC8CP = 8" new construction housing, Chicago Plenum - CCEA compliant	05 = 500 lm 07 = 750 lm 10 = 1000 lm 15 = 1500 lm 20 = 2000 lm 25 = 2500 lm 30 = 3000 lm 35 = 3500 lm 40 = 4000 lm 45 = 4500 lm 55 = 5500 lm 60 = 6000 lm <sup>(7)</sup> 80 = 8000 lm <sup>(7)</sup>	D010=UNV 120-277V, 50/60Hz, 0-10V           1%-100% dimming at 120-277V on 0-10V           controls           Canada Option 500-4000 lumens:           D010347 = 347VAC 50/60Hz 0-10V 1%-100% dimming. For 500, 750, 1000, 1500, 2000, 2500, 3000, 3500, 4000lm models only (*)           Canada Option 4500-8000 lumens:           D010X347 = step down transformer factory installed (with standard "D010" 120V-277V           LED driver). For 4500, 5000, 5500, 6000, 8000lm models only (*)(*)           DLV = Distributed Low Voltage dimming driver 1%-100%, 1000-4000 lumens only. For use with DLVP system only, refer to DLVP specifications for details. *)(*)	REM7 = 7 watt emergency battery pack with remote test / indicator light, use with D010 only <sup>(1)</sup> (2) <sup>(8)</sup> REM14 = 14 watt emergency battery pack with remote test / indicator light, use with D010 only <sup>(1)</sup> (2) <sup>(8)</sup> IEM7 = 7 watt emergency battery pack with integral test / indicator light, use with D010 only <sup>(1)</sup> (2) <sup>(8)</sup> IEM14 = 14 watt emergency battery pack with integral test / indicator light, use with D010 only <sup>(1)</sup> (2) <sup>(8)</sup> BOD7ST = 7.5 watt Bodine self-test emergency battery pack with remote test / indicator light, use with D010 only <sup>(1)</sup> (2) <sup>(8)</sup> WTA = Factory WaveLinx PR0 Tilemount Sensor Kit <sup>(9)</sup> WTK = Factory WaveLinx LITE Tilemount Sensor Kit <sup>(9)</sup> WTN = WaveLinx PR0 Wireless Node without Sensor <sup>(11)</sup> WLN = WaveLinx LITE Wireless Node without Sensor <sup>(12)</sup> REMV7 = 7 watt emergency battery pack with remote test / indicator light, use with DLV only <sup>(1)</sup> (2) <sup>(8)</sup> IEMV7 = 7 watt emergency battery pack with integral test / indicator light, use with DLV only <sup>(1)</sup> (2) <sup>(8)</sup>	HB128APK = L channel hanger bar, 26", pair (replacement) RMB22 = Adjustable wood joist mounting bars, pair, extend to 22" long H347 = 347 to 120V step down transformer, 75VA H347200 = 347 to 120V step down transformer, 200VA WTA = Field WaveLinx PRO Tilemount Sensor Kit <sup>(4)</sup> WTK = Field WaveLinx LITE Tilemount Sensor Kit <sup>(5)</sup>
Notes	Notes (7) Marked Spacing: Center to Cherter of Adjacent Luminaires = 36" Center of Luminaire to Building Member = 18" Minimum overhead = 0.5"	Notes (1) Not available with CP models (6) New Construction ONLY - Not available with retrofit kit models	Notes           (1) Not available with CP models         (2) Not available with D010347 (347V driver)           (3) Ulus for U.S. only         (4) WTA = WaveLinx PRO tilemount sensor kit for daylight dimming, PIR motion sensing, and optional RLTS- Real Time Location Services, use with D010 only (Refer to WaveLinx PRO times specifications)           (5) WTK = WaveLinx PLT tilemount sensor kit for daylight dimming, PIR motion sensing, use with D010 only (Refer to WaveLinx LTE tilepencinations)           (7) WTK = WaveLinx LTE tilemount sensor kit for daylight dimming, PIR motion sensing, use with D010 only (Refer to WaveLinx LTE tilepencinations)           (8) Emergency battry backup options are Non-IC only, and rated for a minimum starting temperature of 0°C           (11) WPI = WaveLinx LTE wireless node provides luminaire-level control with scene and zone configuration without an Integrated sensor; Cannects wirelessly with daylight dimming sensor and PR motion sensor; If desired. Use with 0-10V driver only. Not compatible with 347V or Chicago plenum. (Refer to WaveLinx LTTE wireless node provides luminaire-level control with scene and zone configuration without an Integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor; I desired. Use with 0-100 driver only. Not compatible with 347V or Chi	Notes (4) WTA = WaveLinx PRO tilemount sensor kit for daylight dimming. PIR motion sensing, and optional RUTS - Real Time Location Services, use with DOI only. (Refer to WaveLinx PRO specifications.) (5) WTK = WaveLinx LITE tilemount sensor kit for daylight dimming. PIR motion sensing, use with DOI only. (Refer to WaveLinx LITE specifications.)

### **Quick Spec Emergency Mounting Frame Order Information**

#### Sample Number :

Quick Spec Emergency Mounting Frame: RR-HC820D010REM7

LED module and reflectors are ordered separately. Sample Number: LED Module: HM80520835 | Reflector: 81MDC

#### Select from the Quick Spec Mounting Frame ordering information to receive the *Fast Delivery* option for the frame.

Quick Spec Code	Mounting Frame	Lumens	Driver Options	Factory Installed Emergency & Connected Lighting Options	Accessories (Order & Install Separately)
RR = East Region BRR = West Region	HC8 = 8" new construction downlight housing	<b>15</b> = 1500 lm <b>20</b> = 2000 lm <b>30</b> = 3000 lm <b>40</b> = 4000 lm <b>60</b> = 6000 lm <sup>(7)</sup> <b>80</b> = 8000 lm <sup>(7)</sup>	D019=UNV 120-277V, 50/60Hz, 0-10V 1%-100% dimming at 120-277V on 0-10V controls	REM7 = 7 watt emergency battery pack with remote test / indicator light, use with D010 only <sup>(2)(8)</sup> REM14 = 14 watt emergency battery pack with remote test / indicator light, use with D010 only <sup>(2)(8)</sup> IEM7 = 7 watt emergency battery pack with integral test / indicator light, use with D010 only <sup>(2)(8)</sup> IEM14 = 14 watt emergency battery pack with integral test / indicator light, use with D010 only <sup>(2)(8)</sup>	HB128APK = L channel hanger bar, 26", pair (replacement) RMB22 = Adjustable wood joist mounting bars, pair, extend to 22" long
Notes	Notes	Notes (7) Marked Spacing: Center to Center of Adjacent Luminaires = 36° Center of Luminaire to Building Member = 18° Minimum overhead = 0.5°	Notes	Notes (2) Not available with D010347 (347V driver) (8) Emergency battery backup options are Non-IC only, and rated for a minimum starting temperature of 0°C	Notes



### **LED Module Order Information**

Notes	Notes	840 = 80CRI, 4000K 850 = 80CRI, 5000K	940 = 90CRI, 4000K 950 = 90CRI. 5000K Notes			
HM8 = 8" LED Modules	0520 = 500 - 2000 lumen 2555 = 2500-5500 lumen 6080 = 6000-8000 lumen	827 = 80CRI, 2700K 830 = 80CRI, 3000K 835 = 80CRI, 3500K	927 = 90CRI, 2700K 930 = 90CRI, 3000K 935 = 90CRI, 3500K			
Module	Lumens	CRI / CCT			Lumens CRI / CCT	

### **Trim Order Information**

Reflector	Distribution <sup>(10)</sup>	Finish	Flange	Accessories	
81 = 8" conical reflector	MD = medium reflector 37° beam angle, 0.60 SC     H = Semi-specular clear     Blank = White flange standard with       WD = wide reflector 71° beam angle, 1.08 SC     W = White     WF = White flange option available		Blank = Polished flange standard with C & H reflectors Blank = White flange standard with W reflector WF = White flange option available with C & H reflectors BF = Black flange option available with C, H, & W reflectors	81RWWPK = Replacement part kit - wall wash lens inser - for use with 81RWW* only.	
81 = 8" baffle reflector	WD = wide baffle 71° beam angle, 1.08 SC RWW = rotatable wall wash with linear spread lens (wide beam baffle with lens wall wash)	<b>BB</b> = Black baffle <b>WB</b> = White baffle	Blank = White flange standard with BB & WB reflectors BF = Black flange option available with BB reflectors		
81PS = 8" non-conductive polymer conical reflector <sup>(9)</sup>	<b>MD</b> = medium reflector 37° beam angle, 0.60 SC	W = White	Blank = White flange standard with W reflector BF = Black Flange option available with W reflectors		
Integral Emergency					
81IEM = 8" conical reflector for integral emergency only	ND = narrow reflector 13° beam angle, 0.24 SC MD = medium reflector 37° beam angle, 0.60 SC WD = wide reflector 71° beam angle, 1.08 SC	C = Specular clear H = Semi-specular clear W = White	Blank = Polished flange standard with C & H reflectors           Blank = White flange standard with W reflector           WF = White flange option available with C & H reflectors           BF = Black flange option available with C, H, & W reflectors	IEM = Reflector for IEM only	
81IEM = 8" baffle reflector for integral emergency only	WD = wide baffle 71° beam angle, 1.08 SC	BB = Black baffle WB = White baffle	Blank = White flange standard with BB & WB reflectors BF = Black flange option with BB reflectors	IEM = Reflector for IEM only	
Notes (9) 81PS reflector is for Non-IC environment only, and up to 4000 lumens only	Notes (10) Values are nominal, based on specular clear reflector, other may vary.	Notes	Notes	Notes	



### Product Specifications

#### Frame

- Boat shaped galvanized steel plaster frame with adjustable plaster lip for 1/2" to 1-1/2" thick ceilings
- May be installed in new construction; or from below the finished (non-accessible) ceiling in remodeling.
- Provided with (2) old work clips to secure the frame to the ceiling when remodeling

#### **Universal Mounting Bracket**

- Mounting bracket adjusts 2" vertically from above the ceiling or thru the aperture
- Use with the included mounting bars or with 1/2" EMT (by others)
- Removable to facilitate installation from below the finished ceiling

#### **Mounting Bars**

- Captive preinstalled No Fuss<sup>™</sup> mounting bars lock to tee grid with screwdriver or pliers
- Centering mechanism allows for consistent positioning of fixtures
- Accessory adjustable wood joist mounting bars option available to order separately (requires field replacement of No Fuss bars)

#### **LED Module**

- Proximity phosphors over chip on board LEDs provide a uniform source with high efficiency and no pixilation
- Available in 80 or 90 CRI minimum, provides accuracy within 3 SDCM color uniformity
- 90 CRI, R9>50 (refer to photometry section for colorimetric data)
- Available in 2700K, 3000K, 3500K, 4000K and 5000K correlated color temperature (CCT)
- Lumen options include 500, 750, 1000, 1500, 2000, 2500, 3000, 3500, 4000, 4500, 5000, 5500, 6000, 8000 lumens (nominal)
- Passive thermal management achieves L70 at 60,000 hours in IC and non IC applications (refer to compliance listings)
- Integral diffuse lens provides visual shielding
- Integral connector allows quick connection to housing flex

#### Reflector

- Self-flanged aluminum reflectors are available in narrow, medium or wide distribution patterns
- Medium distribution non-conductive polymer matte white reflector for use in meeting 'dead front' applications
- Wall wash reflector features a rotatable linear spread lens for precise alignment of vertical illumination.
- Reflectors attach to LED module with (3) speed clamps
- Multiple painted or plated finishes are available

#### **Reflector / Module Retention**

 Reflector / module assembly is securely retained in the housing with (2) torsion springs

#### Driver

- Field replaceable constant current driver
- UNV 120-277VAC 50/60Hz input standard;
   Continuous 1% 100% dimension with 0 100%
- Continuous 1% 100% dimming with 0-10V analog controls
- Optional "DLV" low voltage DC driver for Cooper Lighting Solutions DLVP distributed low voltage system combines power and control

#### **Canada Options**

- 347VAC 50/60Hz; 1% dimming on 0 -10V analog control, for 500, 750, 1000, 1500, 2000, 2500, 3000, 3500, 4000 lumen models only
- 347V step down transformer factory installed with the standard "D010" 120V-277V, LED driver on 4500, 5000, 5500, 6000, 8000 lumen models only

#### **Emergency Option**

- Provides 90 minutes of standby lighting meeting most life safety codes for egress
- Available with integral or remote charge indicator and test switch
- Available Self-Test (self-diagnostic), with remote charge indicator and test switch
- Quick Spec emergency ordering option for quickturn projects

#### **Connected Lighting System**

Two WaveLinx connected solutions to choose from. Refer to WaveLinx system specifications and application guides for details.

#### WaveLinx PRO Tilemount Sensor Kit

 WaveLinx PRO WTA tilemount sensor kit offers daylight dimming, PIR motion sensing, scene and zone configuration, automatic commissioning; and optional RLTS - Real Time Location Services available.

#### WaveLinx PRO Wireless Node

 WaveLinx PRO WPN wireless node provides luminaire-level control with scene and zone configuration without an integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with 0-10V driver only. Note: Not compatible with 347V or Chicago plenum.

#### WaveLinx LITE Tilemount Sensor Kit

 WaveLinx LITE WTK tilemount sensor kit offers daylight dimming and PIR motion sensing, scene and grouping configuration.

#### WaveLinx LITE Wireless Node

 WaveLinx LITE WLN wireless node provides luminaire level control with scene and zone configuration without an integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with 0-10V driver only. Note: Not compatible with 347V or Chicago plenum.

#### WaveLinx Tilemount Sensor Kits Application

- The WTA and WTK tilemount sensor kits include a control module mounted on the luminaire junction box via 1/2" knock-out, and a tilemount sensor on 54-inch whip; for ceiling installation by directmount spring clips or via mounting bracket in octagon ceiling boxes.
- The WTA and WTK tilemount sensor kits may be ordered as factory installed on the luminaire, or ordered separately as a field installed accessory kit.
- Note: WaveLinx PRO devices are only compatible with the WaveLinx PRO system.
- Note: WaveLinx LITE devices are only compatible with the WaveLinx LITE system.

#### Junction Box

- Galvanized steel junction box
- 20 in3 internal volume excluding voltage barrier
- · 25 in3 internal total volume
- Voltage divider for 0-10V dimming wires [occupies (1) 1/2" pry-out space]
- Listed for (8) #12 AWG (four in, four out) 90° C conductors and feed-thru branch wiring
- (3) 1/2" and (2) 3/4" trade size pry-outs available
- (3) 4-port push wire nuts for mains voltage, with 1-port for fixture connection

#### Compliance

- cULus Certified to UL 1598 / C22.2 No. 250.0, suitable for damp locations and wet locations in covered ceilings only
- Emergency options provided with UL Listed emergency drivers to UL 924 / C22.2 No. 141, suitable for indoor/damp locations.
- IP20 Above finished ceiling; IP65 - Below finished ceiling
- Non-IC rated 3000, 3500, 4000, 4500, 5000, 5500, 6000, 8000 lumen models. Insulation must be kept 3" from top and sides.
- IC rated 500, 750, 1000, 1500, 2000, 2500 lumen models are suitable for direct contact with air permeable insulation (IC models are also suitable for Non-IC)
- Non-IC marked spacing required for 3500, 4000, 4500, 5000, 5500, 6000, 8000 lumen models
  - Marked Spacing Center to Center of Adjacent Luminaires = 36"
  - Center of Luminaire to Building Member = 18"
    Minimum overhead = 0.5
- · Emergency battery backup options are Non-IC only.
- Not for use in direct contact with spray foam insulation, consult NEMA LSD57-2013
- Airtight per ASTM-E283-04
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements
- EMI/RFI emissions FCC CFR Title 47 Part 15 Class A 120/277V
- · Contains no mercury or lead and RoHS compliant
- Photometric testing in accordance with IES LM-79-08
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11
- 500, 750, 1000, 1500 lumen 90CRI IC rated model may be used to comply with State of California Title 24 residential code, per JA8 certification standards
- May be used to comply with State of California Title 24 non-residential code, in Non-IC, as a dimmable LED luminaire
- ENERGY STAR<sup>®</sup> certified, refer to certified light fixtures database

#### Warranty

• Five year limited warranty, consult website for details. <u>www.cooperlighting.com/legal</u>




## HC8 | HM8 | 81

### **Photometric Data**



#### NARROW DISTRIBUTION - SPECULAR CLEAR FINISH, 2000 LUMEN MODEL, 80 CRI, 3500K

NARR	OW (55° BEAM*)		
Test Number	P575618		
Housing	HC820D010		
Module	HM80520835		
Reflector	81NDC		
Lumens	2237 Lm		
Efficacy	111.8 Lm/W		
SC	0.22		
UGR	11.7		



C	ONE OF	LIGH	Г
o. E		 D 	
ΜН	FC	L	w
5.5'	451.4	1.2	1.2
7'	278.6	1.4	1.4
8'	213.3	1.6	1.6
9'	168.6	1.8	1.8
10'	136.5	2.2	2.2
12'	94.8	2.6	2.6

CANDEL	A TABLE
Degrees Vertical	Candela
0	13653
5	8724
15	2306
25	1331
35	319
45	47
55	3
65	2
75	0
85	2
90	0

ZONAL LUMEN SUMMARY				
Zone	Lumens	% Fixture		
0-30	1946	87		
0-40	2190	97.9		
0-60	2234	99.9		
0-90	2237	100		
90-180	0	0		
0-180	2237	100		

LUMINANCE				
Average Candela Degrees	Average 0° Luminance			
45	2037			
55	161			
65	109			
75	0			
85	531			

#### MEDIUM DISTRIBUTION - SPECULAR CLEAR FINISH, 2000 LUMEN MODEL, 80 CRI, 3500K

	CANDLEPOWER DISTRIBUTION	C	ONE OI	= LIGH	Т	CANDE	A TABLE
st P575617 Imber	Downlight		Δ	т		Degrees Vertical	Candela
usina HC820D010			₀ /¦∖		.	0	4716
using HC820D010			′ /	Ĭ		5	4483
odule HM80520835	4716		$\leftarrow$	} ⊥	.	15	2870
flector 81MDC	3537		1			25	1630
	2358	мн	FC	L	w	35	592
mens 2434 Lm	1179	5.5'	155.9	3.2	3.2	45	93
icacy 121.7 Lm/W	0 90°	7'	96.3	4	4	55	14
0.58	80°	8'	73.7	4.6	4.6	65	3
R 11.8	//0 60°		-	-	-	75	0
	50°	9'	58.2	5.2	5.2	85	0
	0° 10° 20° 30° 4	10'	47.2	5.8	5.8	90	0
	0-deg 45-deg 90-deg	12'	32.8	7	7	L	

ZONAL LUMEN SUMMARY					
Zone	Lumens	% Fixture			
0-30	1954	80.3			
0-40	2339	96.1			
0-60	2431	99.9			
0-90	2434	100			
90-180	0	0			
0-180	2434	100			

LUMIN	IANCE
Average Candela Degrees	Average 0° Luminance
45	4073
55	731
65	219
75	0
85	0








### WIDE DISTRIBUTION - SPECULAR CLEAR FINISH, 2000 LUMEN MODEL, 80 CRI, 3500K

WIDE	E (65° BEAM*)
Test Number	P575620
Housing	HC820D010
Module	HM80520835
Reflector	81WDC
Lumens	2531 Lm
Efficacy	126.5 Lm/W
SC	1.1
UGR	11.6

SC = Spacing Criteria UGR = Unified Glare Rating



CONE OF LIGHT				
МН	FC	L	w	
5.5'	65.1	6	6	
7'	40.2	7.6	7.6	
8'	30.8	8.6	8.6	
9'	24.3	9.8	9.8	
10'	19.7	10.8	10.8	
12'	13.7	13	13	

, 3500	•
CANDEL	A TABLE
Degrees Vertical	Candela
0	1969
5	1909
15	1809
25	1585
35	1107
45	389
55	130
65	15
75	2
85	0
90	0

ZONAL LUMEN SUMMARY					
Zone	Lumens	% Fixture			
0-30	1415	55.9			
0-40	2076	82			
0-60	2510	99.2			
0-90	2531	100			
90-180	0	0			
0-180	2531	100			

LUMINANCE		
Average Candela Degrees	Average 0° Luminance	
45	16947	
55	6962	
65	1094	
75	179	
85	0	

### Photometric Multipliers (Nominal Lumen Values)

500 Lumen	750 Lumen	1000 Lumen	1500 Lumen	2000 Lumen	2500 Lumen	3000 Lumen	3500 Lumen
0.32	0.43	0.53	0.72	1.00	1.24	1.51	1.80
4000 1							
4000 Lumen	4500 Lumen	5000 Lumen	5500 Lumen	6000 Lumen	8000 Lumen		

Multipliers for relative lumen values with other series models.

#### **Color Finish Multipliers**

Finish code	С	н	w	BB
Finish	Specular Clear	Semi-Specular	Matte White	Black Baffle (lower cone)
Multiplier	1.00	0.95	0.91	0.89

\*Value are nominal with specular clear reflectors, other finishes and field results may vary.

Multipliers for relative lumen values with other color finishes.

#### CCT Multipliers - 80CRI

2700K	3000K	3500K	4000K	5000K
0.97	0.96	1.00	1.07	1.07

Multipliers for relative lumen values with other series color temperatures.

#### CCT Multipliers - 90CRI

0.78 0.87 0.92 0.94 0.94	2700K	3000K	3500K	4000K	5000K
	0.78	0.87	0.92	0.94	0.94

Multipliers for relative lumen values with other series color temperatures.




### **Photometric Data**



#### WALL WASH DISTRIBUTION - SPECULAR CLEAR FINISH, 2000 LUMEN MODEL, 80 CRI, 3500K

W	ALL WASH
Test Number	P575619
Housing	HC820D010
Module	HM80520835
Reflector	81RWWC
Lumens	2145 Lm
Efficacy	107.2 Lm/W
SC	1.08



CANDEL	A TABLE
Degrees Vertical	Candela
0	1129
5	1139
15	1127
25	1028
35	803
45	524
55	330
65	197
75	90
85	15
90	0

ZONALI	UMEN SU	JMMARY
Zone	Lumens	% Fixture
0-30	831	38.7
0-40	1278	59.6
0-60	1933	90.1
0-90	2145	100
90-180	0	0
0-180	2145	100

LUMIN	LUMINANCE							
Average Candela Degrees	Average 0° Luminance							
45	22864							
55	17741							
65	14403							
75	10770							
85	5307							

SC = Spacing Criteria, nominal for specular clear reflector, other finishes and field results may vary.

		MULTIP	LE UNIT	FOO	TCANDL	ES	
		5' from w e from fixtu 3 ```				5' from w e from fixtu 4	
1	22.9	20	22.9		21.4	12.5	21.4
2	35.7	35	35.7		32.6	24.7	32.6
3	35.1	36.6	35.1		31.6	27.7	31.6
4	28.4	31	28.4		25.2	25	25.2
5	20.9	23.2	20.9		18.4	19.8	18.4
6	15.1	16.6	15.1		13.3	14.8	13.3
7	11	11.9	11		9.8	10.9	9.8
8	8.1	8.7	8.1		7.3	8.1	7.3
9	6.1	6.4	6.1		5.6	6.1	5.6
10	4.6	4.9	4.6		4.3	4.7	4.3
	1						

	;	SINGLE	UNIT	FOOTO	ANDL	ES						
	2.5' from wall (distance from fixture along wall)											
1	20.6	14.6	6.2	2.3	0.8	0.3	0.1					
2	30	23.2	12.3	5.7	2.6	1.2	0.6					
3	27.9	23	13.8	7.2	3.7	1.9	1					
4	21	18.3	12.5	7.4	4.1	2.3	1.3					
5	14.3	13	9.9	6.6	4.1	2.5	1.5					
6	9.7	9	7.4	5.4	3.7	2.4	1.6					
7	6.7	6.3	5.5	4.3	3.2	2.2	1.5					
8	4.7	4.5	4	3.4	2.6	1.9	1.4					
9	3.4	3.3	3.1	2.6	2.1	1.7	1.3					
10	2.6	2.5	2.3	2.1	1.7	1.4	1.1					

#### Photometric Multipliers (Nominal Lumen Values)

500 Lumen	750 Lumen	1000 Lumen	1500 Lumen	2000 Lumen	2500 Lumen	3000 Lumen	3500 Lumen
0.32	0.43	0.53	0.72	1.00	1.24	1.51	1.80
4000 Lumen	4500 Lumen	5000 Lumen	5500 Lumen	6000 Lumen	8000 Lumen		

Multipliers for relative lumen values with other series models.

#### **Color Finish Multipliers**

Finish code	С		W	BB
Finish	Specular Clear	Semi-Specular	Matte White	Black Baffle (lower cone)
Multiplier	1.00	0.95	0.91	0.89

Multipliers for relative lumen values with other color finishes.

#### CCT Multipliers - 80CRI

2700K	3000K	3500K	4000K	5000K
0.97	0.96	1.00	1.07	1.07

Multipliers for relative lumen values with other series color temperatures.



CCT Multipliers – 90CRI


2700K	3000K	3500K	4000K	5000K
0.78	0.87	0.92	0.94	0.94


Multipliers for relative lumen values with other series color temperatures.


Note: Refer to IES files for more product data.

### **Energy and Performance Data**

#### COLOR METRICS - TM-30-15 & CRI/CIE (3500K)







#### **ENERGY DATA**

Series	500 l	umen	imen 750 lumen		1000 lumen		1500 lumen		2000 lumen	
Input Voltage 120-277VAC	120V	277V	120V	277V	120V	277V	120V	277V	120V	277V
Input Current (A)	0.051	0.026	0.067	0.036	0.083	0.039	0.119	0.053	0.171	0.077
Input Power (W)	6.1	6.5	7.9	8.3	10	10.4	14.5	14.5	20.9	20.6
In-rush (A)	1.9	8.4	2	8.4	2.2	8.5	2.7	8.5	2.1	9.7
Inrush duration (µs)	251	135	237	133	250	134	250	139	245	131
THD (%)	6.2	13.5	7.4	8.8	5.4	10.3	10	6.7	6.5	7.9
PF	≥ 0.99	≥ 0.9	≥ 0.98	≥ 0.92	≥ 0.99	≥ 0.95	≥ 0.99	≥ 0.97	≥ 0.99	≥ 0.96

Series	2500	lumen	3000 lumen		3500 lumen		4000 lumen		4500 lumen	
Input Voltage 120-277VAC	120V	277V	120V	277V	120V	277V	120V	277V	120V	277V
Input Current (A)	0.2	0.088	0.24	0.107	0.292	0.152	0.351	0.159	0.384	0.172
Input Power (W)	23.9	23.8	28.6	28.5	34.6	35.1	42.1	42.1	45.9	45.6
In-rush (A)	2.1	9.9	2.5	11.6	3.4	13.9	3.1	14.7	3.1	14.8
Inrush duration (µs)	244	137	216	111	183	95	200	98	202	100
THD (%)	8.7	6.7	7.8	8.3	5.6	10	4.1	9.5	4.5	8.5
PF	≥ 0.99	≥ 0.96	≥ 0.99	≥ 0.96	≥ 0.99	≥ 0.93	≥ 0.99	≥ 0.94	≥ 0.99	≥ 0.95

Series	5000 lumen		5500 lumen		6000 lumen		8000 lumen	
Input Voltage 120-277VAC	120V	277V	120V	277V	120V	277V	120V	277V
Input Current (A)	0.419	0.186	0.457	0.201	0.489	0.214	0.61	0.29
Input Power (W)	50.1	49.5	54.6	53.7	58.4	57.4	72.5	72.9
In-rush (A)	3.1	15	3.2	14.8	3.4	14.8	6.8	12.9
Inrush duration (µs)	202	117	196	131	192	121	119	109
THD (%)	5.5	7.6	7	7.2	8.1	7.2	10.1	18.6
PF	≥ 0.99	≥ 0.96	≥ 0.99	≥ 0.96	≥ 0.99	≥ 0.97	≥ 0.98	≥ 0.91

Minimum starting temperature -30°C (-22°F)\*

(Nominal input 120-277VAC & 100% of rated output power)

Sound Rating: Class A standards

#### Notes:


\* Emergency Battery packs are rated for a minimum starting temperature of 0°C.




## HC8 | HM8 | 81

### **Dimensional Details**

#### NEW CONSTRUCTION








## HC8 | HM8 | 81

## **Connected Solutions**



I I I I I 120-277 VAC 3A downlights with 0-10V control WaveLinx Sensor and founting Trim (included)

WaveLinx PRO controlled




## HC8 | HM8 | 81

### Connected Solutions

Lighting Solutions

a (signify business



P: 770-486-4800

www.cooperlighting.com

Specifications and dimensions

subject to change without notice.

PS517008EN page 11