

## DESCRIPTION

A 7-3/8" aperture recessed downlight for slope-ceiling applications uses 150/250 or 400/500 Watt frosted T4 Quartz Halogen lamps provides high efficiency and low aperture brightness. Available in 17740-Narrow, 17750-Medium, or 17760-Wide beam distribution. Performance is free from hot spots, filament images, or striations. Housing is top accessible.

Ideal for applications with high ceilings requiring high levels of illumination with long throws and good optical control.

Catalog #	Type
Project	
Comments	Date
Prepared by	

## SPECIFICATION FEATURES

### A ... Housing

Full housing protects optics and adjustment mechanism. Removable cover provides top access. Painted optical matte black to minimize stray light. Die cast 1-1/2" deep aluminum collar accommodates extra thick ceiling construction. Housing is top accessible.

### B ... Optical Assembly

Optical assembly consists of an ellipsoidal primary reflector and parabolic shielding cone. Available in narrow, medium, and wide distribution and sold as an assembly to insure optimum optical performance.

### C ... Upper Reflector

Spun 0.060" thick high purity aluminum reflector with specular clear Alzak® finish. Reflector is mounted to stamped steel frame allowing rapid field installation. Alignment tabs and collar provides correct focus for all three distributions eliminating installation errors.

### D ... Lower Cone

Spun 0.060" thick high purity aluminum cone is available in all standard and special cone colors. Lower cone assembly attaches with torsion springs eliminating gaps with the ceiling surface. Angle cut cone is keyed to prevent improper orientation to the lamp. Available with self flanged or molded trim ring.

### E ... Containment Barrier

Glass lamp shield securely attaches to lower cone assembly allowing easy removal and bottom lamp access.

### F ... Socket Housing

Socket assembly houses mini-can (E11) socket. Lamp and socket are field replaceable from above or below. Integral die cast aluminum heat sink conducts heat away from lamp base and socket at all aiming angles greatly extending life. Securely attaches to upper reflector mounting bracket providing proper lamp position for all distributions.

### G ... Aiming Mechanism

Provides 365° rotation and 30° tilt, adjusts smoothly and locks into any aiming position. Translating center beam optics maintains efficiency at all aiming angles.

### H ... Junction Box

Listed for eight #12 AWG (four in, four out) conductors feed through 90° C branch wiring. Pry-outs for four 1/2" and two 3/4" inch conduits. Junction box can be accessed through aperture by removing cover.

### I ... Insulation Detector

Self-resetting insulation detector opens circuit if insulation is improperly installed.

### Labels


Meets UL1598, cULus listed / certified for damp location. Insulation must be kept 3" from fixture.



**HA7250QT4**  
**HA7500QT4**  
**17761/17760**  
 Wide Beam

**250W or 500W Quartz**  
 T4 Lamp

**7-3/8" APERTURE**  
**ADJUSTABLE RECESSED**  
 Top Accessible




## ORDERING INFORMATION

Sample Number: Complete unit consists of housing, ballast and trim.

Housing	Options	Trims	Finish	Option	Accessories
<b>HA7:</b> 7" T4 Quartz Slope/Directional	<b>CP:</b> Chicago Plenum	<b>17761:</b> WB Self Flanged Reflector	<b>LI:</b> Low Iridescent Clear	<b>WF:</b> White Painted Flanged (Self Flanged only)	<b>H277:</b> Step Down Transformer, 300VA Max
<b>Wattage</b>	<b>DR150:</b> DeRated Wattage Label, 150W Max	<b>17760:</b> WB Reflector	<b>H:</b> Haze		<b>HB26:</b> C Channel Bar Hangers, 26" Long, Pair
<b>250QT4:</b> 150/250W T4 QZ	<b>DR400:</b> DeRated Wattage Label, 400W Max		<b>WMH:</b> Warm Haze		<b>HB50:</b> C Channel Bar Hangers, 50" Long, Pair
<b>500QT4:</b> 400/500W T4 QZ			<b>G:</b> Gold		<b>TRM7:</b> Metal Trim Ring, Specify Finish
			<b>WH:</b> Wheat		<b>TRR7:</b> Rimless Trim Ring, White
			<b>B:</b> Specular Black		<b>FK5:</b> 5 Amp Field Installable Fuse Kit 300V Max
			<b>W:</b> Gloss White		<b>RMB-22:</b> Wood Joist Bar Hanger, 22" Long, Pair
			<b>GP:</b> Graphite		
			<b>GPH:</b> Graphite Haze		
			<b>K:</b> Cognac		
			<b>KH:</b> Cognac Haze		

Candlepower Distribution Curve



Spacing Criteria = 1.22  
 Efficiency = 68.3%

Test No. H22573  
 HA7500QT4 17760LI  
 Lamp = 500W QTZ T4  
 25° Slope

500W  
 QTZ T4

Cone of Light

Distance Fixture to Lighted Plane	Initial Footcandles at Nadir	Beam Diameter
12'0"	73	8'6"
15'0"	46	11'0"
20'0"	26	14'0"
25'0"	17	18'0"
30'0"	12	21'6"

Coefficients of Utilization

Ceiling Wall % RCR	80%				70%			50%	
	70	50	30	10	50	30	10	50	10
Zonal cavity method -- floor reflectance = 20%									
0	81	81	81	81	79	79	79	76	76
1	78	76	74	73	74	73	71	72	69
2	74	71	68	66	69	67	65	67	64
3	70	66	63	60	65	62	60	63	59
4	67	62	58	55	61	58	55	60	54
5	63	58	54	51	57	54	51	56	50
6	60	54	50	47	54	50	47	53	47
7	57	51	47	44	51	47	44	50	44
8	55	48	44	41	48	44	41	47	41
9	52	45	41	39	45	41	39	44	39
10	50	43	39	36	43	39	36	42	36