


Good

Better


Best

Click on products  
to learn more



		WSL	Hugo	RZL	Jaylum	Iridium i3	Continua CTA
APPLICABILITY¹	Education	★★	★★★	★★	★★★	★★★	★★★
	Office	★★★	★★	★	★★★	★★	★★
	Healthcare	★★	★★	★★	★★	★★	★★
	Retail	★★★	★★★	★★★	★	★	★★
FEATURES / PERFORMANCE	Construction	Cold Rolled Steel	Extruded Aluminum	Cold Rolled Steel	Cold Rolled Steel	Cold Rolled Steel	Extruded Aluminum
	Lengths	4', 8', Cont.	4', 8', 12', Cont.	4', 8', 12', Cont.	4', 8', Cont.	4', 8', Cont.	4', 8', 12', Cont.
	Im/W (Max)	121	145	135	157	158	147
	Lumens (Max)	8000 (2000 lms/ft)	8000 (2000 lms/ft)	8800 (2200 lms/ft)	8000 (2000 lms/ft)	8000 (2000 lms/ft)	6000 (1500 lms/ft)
	Up/Down % Options	3	2	2	5	5	4+
	CIE Type	Direct, Semi-Direct	Direct, Semi-Direct	Direct, Semi-Direct	Direct/Indirect	Direct/Indirect	Direct, Direct/Indirect
	Life (@60K)	L81	L85	L85	L93	L93	L84
	Shielding	WaveStream - Acrylic	Frost - Smooth, Drop Lens, Baffle	Frost -Linear Prismatic, Baffle	Frost - Smooth	Frost - Smooth	Frost - Continuous Roll Lens
	Companion Family Fixtures	Surface	Surface	Surface	Wall, Sconce	-	Wall
	Driver Location	Integral	Integral	Integral	Integral	Integral	Integral
	Emergency	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated
	CRI	80+	80+ / 90	80+ / 90	80+ / 90	80+ / 90	80+ / 90
	Sensor Location	Integrated	Integrated, Side Mount	Integrated	Integrated	Integrated	Integrated, Side Mount
	DLC	Standard	Premium	Premium	Premium	None	Premium
	VividTune™	No	No	No	Tunable White	Tunable White	No
INTEGRATED CONTROLS	Stand Alone Daylight / Occupancy	✓		✓	✓	✓	
	WaveLinx	✓	✓	✓	✓	✓	✓
	Enlighted	✓	✓	✓	✓	✓	✓
	DLVP	✓					

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable



		Continua SQ4	Iridium i2 WaveStream	Divide	Vaulta	Discreet	Cirque
APPLICABILITY¹	Education	★★★	★★★	★★	★★	★★	★★
	Office	★★★	★★	★★★	★★★	★★★	★★★
	Healthcare	★★	★★	★	★★	★★	★★
	Retail	★★	★	★★	★★	★★	★
FEATURES / PERFORMANCE	Construction	Extruded Aluminum	Cold Rolled Steel	Extruded Aluminum	Extruded Aluminum	Extruded Aluminum	Extruded Aluminum
	Lengths	4', 6', 8', 12', Cont.	4', 8', Cont.	4', 8', Cont.	4',6', 8', 12' Cont.	4',6', 8', 12' Cont.	4',6', 8', 12' Cont.
	Im/W (Max)	135	114	140	127	127	164
	Lumens (Max)	10,800 lm (2,700 lms/ft)	7200 (1800 lms/ft)	6000 (1500 lms/ft)	1250 (1500 lms/ft)	11920 (2980 lms/ft)	1500 (2475 lms/ft)
	Up/Down % Options	20+	3	2	28+	28+	28+
	CIE Type	Direct, Direct/Indirect	Direct, Direct/Indirect	Direct, Direct/Indirect	Direct, Direct/Indirect	Direct, Direct/Indirect	Direct, Direct/Indirect, Indirect
	Life (@60K)	L84	L81	L87	L85	L85	L90
	Shielding	Frost - Continuous Roll Lens	Frost - Linear Prismatic	WaveStream - Acrylic Specular, Diffuse	Discrete Optics, Black or White Baffles	Discrete Optics, Black or White Baffles	Discrete Optics, Black or White Baffles
	Companion Family Fixtures	Recessed	-	Surface, Wall, Recessed	Surface	Surface	Surface
	Driver Location	Integral	Integral	Integral	Integral	Integral	Integral
	Emergency	Integrated	Integrated	Integrated	Integrated	Integrated	Integrated
	CRI	80+ / 90	80+ / 90	80+ / 90	80+ / 90	90+	80+ / 90
	Sensor Location	Integrated, Endcap/Side Mount	Integrated	Integrated	Integrated	Integrated	Integrated
	DLC	Premium	Standard	Premium	In-process	In-process	In-process
	VividTune™	No	No	No	No	No	No
INTEGRATED CONTROLS	Stand Alone Daylight / Occupancy		✓				
	WaveLinx	✓	✓	✓	✓	✓	✓
	Enlighted	✓	✓	✓	✓	✓	✓
	DLVP						


Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable

# Architectural LED

## Linear Suspended

Best

Click on products  
to learn more



		Omni	Define	Converge	Covera
APPLICABILITY <sup>1</sup>	Education	★★	★★	★★★	★★★
	Office	★★★	★★★	★★★	★★★
	Healthcare	★★	★★	★	★
	Retail	★	★	★★	★★
FEATURES / PERFORMANCE	Construction	Extruded Aluminum	Extruded Aluminum	Extruded Aluminum	Metal cast
	Lengths	4', 6', 8', 12' Cont.	2' - 12', Cont.	4', 8', Cont.	2', 4'
	lm/W (Max)	121	164	119	157
	Lumens (Max)	1500 (2475 lms/ft)	9900 (2475 lms/ft)	6700 (1700 lms/ft)	8000 (2000 lms/ft)
	Up/Down % Options	28+	∞	3	2
	CIE Type	Direct, Direct/Indirect, Indirect	Direct, Direct/Indirect, Indirect	Direct, Direct/Indirect	Direct/Indirect
	Life (@60K)	L90	L90	L85	L93
	Shielding	Discrete Optics, Black or White Baffles	Frost - Smooth, Drop & Regressed, Asymmetric and Batwing Lens	WaveStream - Acrylic Diffuse	Frost - Smooth
	Companion Family Fixtures	Surface	Surface, Wall, Recessed, Perimeter	-	-
	Driver Location	Integral	Integral	Remote w/ Luxwire	Integral
	Emergency	Integrated	Integrated	Remote	Integrated
	CRI	80+ / 90	80+ / 90	80+ / 90	80+ / 90
	Sensor Location	Integrated	Integrated	Tile Mount	Integrated
INTEGRATED CONTROLS	DLC	In-Process	Premium	None	None
	VividTune™	No	Tunable White	No	No
	Stand Alone Daylight / Occupancy		✓	✓	✓
	WaveLinx	✓	✓	✓	✓
	Enlighted	✓	✓	✓	✓
	DLVP			✓	

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable



**Cooper Lighting Solutions**  
1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
www.cooperlighting.com

**Canada Sales**  
5925 McLaughlin Road  
Mississauga, Ontario L5R 1B8  
P: 905-501-3000  
F: 905-501-3172

© 2023 Cooper Lighting Solutions  
All Rights Reserved  
Publication No. SA524005EN-web  
July 30, 2023 5:35 PM

Cooper Lighting Solutions is a registered trademark.  
All other trademarks are property of their respective owners.  
Product availability, specifications, and compliances are subject to change without notice.