



## WaveLinx Connected Lighting

# Classroom

example 2



	Manually Switched ON / OFF	Manual Dimmer	Manual ON / Auto OFF	Occupancy Sensor	Daylighting Control	Lumen Maintenance Control	Tuning Control	Receptacle Control	Demand Response
IECC 2018	•	•	•	•	•	•	•	•	•
ASHRAE 90.1 - 2019	•	•	•	•	•	•	•	•	•
T24 2019	•	•	•	•	•	•	•	•	•
NECB 2017	•	•	•	•	•	•	•	•	•



### Sequence of Operations

#### Lighting

- 0-10V lighting loads
- Up to 3 dimmable zones
- Out of the box 75% high end trim

#### Occupancy

- Automatic auto on to 50%
- Optional vacancy mode
- Optional auto on to scene
- Plug load turns on with occupancy (optional for IECC)
- Automatic off of lighting and plug load on vacancy

#### Daylighting

- Continuous dimming to off
- Individual luminaire daylight dimming to approximately 500 lux
- Daylighting not required for indoor spaces without windows
- Not required in spaces without windows or that are less than 150W (120W for ASHRAE / Title 24)

#### Manual Controls

- Programmable scenes
- Dominant button is 50% light level
- Scene raise / Scene lower
- All off


#### Additional Features

- Energy calculations (available through Trellix)
- Automatic demand response through wireless area controller
- Scheduling of partial off light levels from wireless area controller
- UL924 emergency control capabilities via luminaire battery backup or fixture integrated transfer device (consult fixture spec sheet)
- Complies with Enhanced Digital Lighting Control section C406 (IECC)

### Bill of Material

Quantity	Catalog #	Description
1	WAC-POE	Wireless Area Controller
1	W4S-RL-W	WaveLinx Wallstation
1	WR-20	WaveLinx Receptacle (ASHRAE / Title 24)
12	24EN-LD2-34-UNV-L835-CD1-WAA-U	Encounter 2x4 with WaveLinx Sensor

### Typical Wiring Detail



	Design Consideration	Best Practice	Maximum
	Gateway / Wireless Area Controller range	150 ft LOS	300 ft LOS
	Number of interior walls	2 walls	3 walls
	Distance from Wireless Area Controller to 1st WaveLinx device	150 ft	200 ft
	Distance between WaveLinx devices	75 ft	150 ft
	Number of hops from Wireless Area Controller	4 hops	5 hops
	Number of areas per Wireless Area Controller	15 + 1 construction area	
	Number of zones per area	3	16
	Number of scenes per area	16	16

	Local Control	Manual ON	Partial ON	Bilevel Lighting	Daylight Side	Daylight Top	Partial OFF	Automatic OFF	Scheduled OFF	Receptacle Control	Energy Monitoring	Parking Garage	Functional Testing	Demand Response	Enhanced Digital
IECC 2018	C405.2.5	C405.2.5	C405.2.1.2		C405.2.3.2	C405.2.3.3	C405.2.1.3	C405.2.1.1.1	C405.2.2	C405.2.4		C405.2.6	C408.3		C406.4
ASHRAE 90.1-2019	9.4.1 (a)	9.4.1.1 (b)	9.4.1.1 (c)	9.4.1.1 (d)	9.4.1.1 (e)	9.4.1.1 (f)	9.4.1.1 (g)	9.4.1.1 (h)	9.4.1.1 (i)	8.4.2	8.4.3.2	9.4.1.2	9.4.3		C406.4
T24 2019	130.1 (a)(b)	130.1 (a)(b)	130.1 (b)		130.1 (d)	130.1 (d)	130.1 (c).6	130.1 (c).5	130.1 (c)	130.5 (d)	130.5 (b)	130.1 (d)	130.4	130.1 (a) 130.1 (e)	
NECB 2017	4.2.2.1.(3)	4.2.2.1.(3), 4.2.2.1.(6)	4.2.2.1 (8)	4.2.2.1.(9)	4.2.2.1.(10)	4.2.2.1.(13)	4.2.4.1, (16-17)	4.2.2.1, (18-19)	4.2.2.1, (20-23)			4.2.2.2 4.2.2.4			