


Project		Catalog #		Type	
Prepared by		Notes		Date	



HALO

H27T

6" Non-Insulated Shallow Ceiling Recessed Housing

Typical Applications

Residential, Light Commercial

Interactive Menu

- Order Information [page 2](#)
- Product Specification [page 3](#)
- Product Warranty



Product Certification



Top Product Features

- Got Nail!™ bar hangers
- Pass-N-Thru™ tool-less shortening of bar hangers
- Slide-N-Side™ wire traps
- Quick Connect wiring connectors included in junction box
- Thermally protected
- Options to meet Trade Agreements Act requirements

Dimensional and Mounting Details






















Order Information Continued

SAMPLE ORDER NUMBER: **H27T-426RG**

Order housing, trim and accessories separately.




Domestic Preferences	Housing
Domestic Preferences ⁽¹⁾	Housing
[Blank] =Standard TAA =Trade Agreements Act	H27T = 6" Non-Insulated Shallow Ceiling Housing
(1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to DOMESTIC PREFERENCES website for more information. Components shipped separately may be separately analyzed under domestic preference requirements.	

Trims

Reflectors	Baffles	Eyeballs and Adjustables	Lens Trims
 426 Specular Reflector Cone 100W R30 OD: 7 1/4" [184mm] 426 = Specular Clear 426H = Haze 426RG = Residential Gold 426CG = Champagne Gold 426MB = Specular Black	 310 Baffle 75W R30 OD: 7 1/4" [184mm] 310P = Black Baffle 310W = White Baffle	 74 Eyeball - 30° Tilt 75W PAR30 OD: 8" [203mm] 74P = White Eyeball	 70 Albalite Lens 60W A19 OD: 8" [203mm] 70P = Albalite Lens with White Trim Ring 70PS = Albalite Lens Showerlight with White Trim Ring
 429 Dayform White Cone 75W R30 OD: 7 1/4" [184mm] 429P = White Cone		 77 Eyeball 50W R20, 50W PAR20 OD: 8" [203mm] 77P = White Eyeball	 170 Albalite Lens w Reflector 60W A19 OD: 8" [203mm] 170P = Albalite Lens with White Trim Ring - Socket Supporting
 4261 Self Flanged Reflector Cone 100W R30 OD: 7 1/4" [184mm] 4261P = White Self Flanged Reflector Cone		 78 Eyeball - 30° Tilt 75W R30, 75W PAR30 OD: 8" [203mm] 78P = White Eyeball 78SL = Silver Eyeball 78B = Brass Eyeball 78PB = Polished Brass Eyeball 78PAT = White AIR-TITE Eyeball	 71 Drop Opal Lens 60W A19 OD: 8" [203mm] 71P = Drop Opal Lens with White Trim Ring
		 90 Double Bubble - 60° Tilt 250W PAR38 OD: 8" [203mm] 90P = White Double Bubble Adjustable	 171 Drop Opal Lens 60W A19 OD: 8" [203mm] 171P = Drop Opal Lens with White Trim Ring - Socket Supporting
		 376 Adjustable 75W PAR30 OD: 7 1/4" [184mm] 376P = Black Baffle, Black Lampholder, White Trim Ring	 73 Fresnel Lens 60W A19 OD: 8" [203mm] 73P = Fresnel Lens with White Trim Ring
		 378 Adjustable with Splay Reflector 75W PAR30 OD: 7 3/4" [197mm] 378 = White Lampholder with Clear Splay 378P = White Lampholder with White Splay	 173 Fresnel Lens 60W A19 OD: 8" [203mm] 173P = Fresnel Lens with White Trim Ring - Socket Supporting
		 419 Regressed Eyeball with Splay 75W PAR30 OD: 7 1/4" [184mm] 419 = White Eyeball with Clear Splay 419P = White Eyeball with White Splay	 75 All-Glas 60W A19 OD: 7 3/4" [197mm] 75 = All-Glas Diffuser
		 420 Coilex Baffle Eyeball 75W BR30, 75W PAR30L OD: 7 1/4" [184mm] 420P = White Eyeball with Black Baffle 420PB = Polished Brass Eyeball with Black Baffle 420W = White Eyeball with White Baffle	

Trims

Open Trims

Open Trims	
	79 Pinhole Trim 75W PAR30, 65W BR30 OD: 8" [203mm] 79P = White Pinhole Trim
	301 Open 75W R30 OD: 8" [203mm] 301P = White Open Trim 301PB = Polished Brass Open Trim
	328 Splay Trim 100W R30, 75W PAR30, 65W BR30 OD: 7-1/4" [184mm] 328P = White Splay Trim

Accessories

Accessories
Metal Trim Rings Compatible with 310, 312, 376, 378, 426, 419, 420 TRM6P = White Metal TRM6PB = Polished Brass TRM6C = Chrome TRM6MB = Black Metal TRM6SL = Silver Metal TRP7MB = Black Plastic
Oversize Trim Rings For use when ceiling opening is cut too large. Compatible with 310, 312, 376, 378, 419, 420, 426, 429 OT400P = 9 1/4" White Metal OT403P = 8" White Plastic
Step Down Transformer Steps 277V line voltage down to 120V fixture operating voltage. 150VA max. H277 = 150VA Max.
Power-Trac Adapter Trim Allows 120V Trac lampholders (150W Max.) to be used with recessed installations 477P = Black Baffle, white trim ring 477W = White Baffle, white trim ring

Product Specifications

A Housing

Die-stamped 20 gauge CRS with white powder coat finish.

B Socket Plate

Rigid socket plate adjusts and locks without tools for various lamp sizes.

C Plaster Frame

Housing adjusts in plaster frame 1 3/8" to accommodate different ceiling thicknesses. Includes locking screws for hanger bars and cutouts for crimping hanger bars in position

D Junction Box

U.L. listed for through branch circuit wiring. Positioned to accommodate straight conduit runs. Seven conduit knockouts are uniform 1/2" size with true pryout slots. Four Romex pryouts with integral strain relief also included.

E GOT NAIL! Pass-N-Thru™ Bar Hangers

Bar Hanger Features include:

- Pre-installed nail easily installs in regular lumber, engineered lumber and laminated beams
- Safety and guidance system prevents snagging, ensures smooth straight nail penetration and allows bar hangers to be easily removed if necessary.
- Automatic leveling flange aligns the housing and lets you hold the housing in place with one hand while driving nails
- Housing can be positioned at any point within 24" joist span
- Score lines allow "toolless" shortening for 12" joists
- Bar hangers may be repositioned 90°
- Bar hangers do not need to be removed from frame for shortening
- Integral T-bar clips snaps onto T-bars - no additional clips required

F Socket

Porcelain socket with nickel plated brass screw shell.

G Thermal Protector

Integral Thermal Protector deactivates fixture if an incorrect lamp is used or if ceiling insulation material is not applied correctly.

Labels

- U.L. listed for Damp Location
- U.L. listed for Feed Through
- CSA Certified