

Good

Better

Best

Click on products to learn more



|                            |                                  | SLES <sup>2</sup>          | ST                         | ST2 DIM          | SLSTP                       | SSRK Retrofit  | SNX                            | SRL               | MicroBay       |
|----------------------------|----------------------------------|----------------------------|----------------------------|------------------|-----------------------------|----------------|--------------------------------|-------------------|----------------|
| Applicability <sup>1</sup> | Education                        | ●●                         | ●                          | ●●               | ●●●                         | ●              | ●●●                            | ●●●               | ●●●            |
|                            | Office                           | ●                          | ●                          | ●●               | ●●●                         | ●              | ●●●                            | ●●●               | ●●●            |
|                            | Healthcare                       |                            |                            |                  | ●                           | ●              | ●●                             | ●●                | ●●             |
|                            | Retail                           | ●●●                        | ●                          | ●●               | ●●                          | ●●●            | ●●●                            | ●●●               | ●●●            |
|                            | Industrial                       | ●●                         | ●●                         | ●●               | ●●                          | ●●●            | ●●●                            | ●●●               | ●●●            |
|                            | Residential                      |                            | ●●●                        |                  | ●●                          |                |                                |                   |                |
| Features / Performance     | Length                           | 4', 8'                     | 2', 4', 8'                 | 2', 4', 8'       | 2', 4', 8'                  | 4', 8'         | 2', 4', 8'                     | 4', 8'            | 2', 4', 8'     |
|                            | lm/W (Max)                       | 167 (8ft)                  | 108                        | 122              | 148                         | 159            | 176                            | 149               | 175            |
|                            | Lum (Max)                        | 8,700                      | 9,200                      | 9,200            | 11,900                      | 8,000 / 4 ft.  | 22,000                         | 11,000            | 20,000         |
|                            | Life (@60K)                      | L70/50K <sup>3</sup>       | L70/50K                    | L70/50K          | L70/50K                     | L94            | L87                            | L82               | L87            |
|                            | Voltage                          | UNV                        | UNV                        | UNV              | 120V, UNV, NUV (120-347V)   | UNV            | UNV, 347, 480V                 | UNV, 347, 480V    | UNV, 347, 480V |
|                            | Dimming                          | N/A                        | No                         | 0-10V            | Triac or 0-10V <sup>5</sup> | 0-10V          | 0-10V, Step, Dali              | 0-10V, Step, Dali | 0-10V, Dali    |
|                            | Lens                             | None <sup>4</sup>          | White, Single or Dual Lens | White, Dual Lens | Diffuse, Poly               | Frost, Acrylic | Open, Round, FDL, Square, Refl | Frost, Acrylic    | Multiple       |
|                            | Emergency                        | Integrated                 | None                       | Integrated       | Integrated                  | Integrated     | Integrated                     | Integrated        | Integrated     |
|                            | CRI                              | 80+                        | 80+                        | 80+              | 80+                         | 80+            | >80 / 90                       | 80+               | 80+ / 90+      |
|                            | Sensor Location                  | Remote                     | Remote                     | Remote           | Sensor Kit                  | N/A            | Integrated                     | Integrated        | Integrated     |
|                            | DLC                              | Standard (TLED Lamps only) | Standard                   | Standard         | Standard                    | Premium        | Premium                        | Premium           | Premium        |
|                            | Lumen / CCT Select               | No                         | No                         |                  |                             | No             | Yes, specific lumen only       | No                |                |
| Integrated Controls        | Basic Occupancy                  |                            |                            |                  | ✓                           | ✓              | ✓                              | ✓                 | ✓              |
|                            | Stand Alone Daylight / Occupancy |                            |                            |                  |                             | ✓              | ✓                              | ✓                 | ✓              |
|                            | WaveLinX LITE                    |                            |                            |                  |                             | ✓              | ✓                              | ✓                 | ✓              |
|                            | WaveLinX                         |                            |                            |                  |                             | ✓              | ✓                              | ✓                 | ✓              |

Notes: 1. ●●● = high applicability, ●● = medium applicability, ● = low applicability, blank = non-applicable. 2. w/ T8 LED lamps included. 3. TLED lamp tested to B50 L70 requirement. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). 4. TLED CorePro lamp is glass tube. TLED MasterClass lamp is shatter resistant plastic. 5. 0-10V only applies to UNV or NUV inputs.

Good

Better

Best

Click on products to learn more



|                                  |                     | WP                   | NWS                   | ProWrap                              | BCLED         | AWS / AWWS                                | SWLED                             |
|----------------------------------|---------------------|----------------------|-----------------------|--------------------------------------|---------------|---|-----------------------------------|
| Applicability <sup>1</sup>       | Education           | ●●                   | ●●●                   | ●●●                                  | ●●            | ●●●                                       | ●●●                               |
|                                  | Office              | ●                    | ●●                    | ●●●                                  | ●             | ●●●                                       | ●●●                               |
|                                  | Healthcare          | ●                    | ●                     | ●●                                   | ●●            | ●●  | ●                                 |
|                                  | Retail              | ●                    | ●●                    | ●                                    | ●             | ●●●                                       | ●                                 |
|                                  | Industrial          | ●                    | ●●                    | ●●                                   |               | ●   | ●●                                |
|                                  | Residential         | ●●●                  |                       | ●●●                                  | ●             | ●●  |                                   |
| Features / Performance           | Sizes               | 2' and 4', 5.1" wide | 2', 4' / 5.3" wide    | 4' long, 8.8" and 14.8" wide         | 2', 4'        | 2', 4', 8' / 5.5" & 10" Wide              | 4'                                |
|                                  | lm/W (Max)          | 114                  | 129                   | 141                                  | 120           | 165                                       | 150                               |
|                                  | Lum (Max)           | 3,400                | 4,900                 | 6000 (8.8") / 8000 (14.8")           | 4,800         | 13,000                                    | 8,000                             |
|                                  | Life (@60K)         | L70/50K              | L82                   | L85                                  | L82           | L90                                       | L91                               |
|                                  | Lens                | Prismatic Acrylic    | Diffuse, Acrylic      | Microprism Acrylic                   | Frost, Smooth | (Vandal Resistant) Ribbed Frost, Polycarb | (Vandal Resistant) Frost, Acrylic |
|                                  | Emergency           | No                   | Remote                | Integrated (10W)                     | Integrated    | Integrated                                | Integrated                        |
|                                  | CRI                 | 80+                  | 80+                   | 80+                                  | 80+           | 80+, 90+                                  | 80+                               |
|                                  | Row Mount           | N/A                  | Yes                   | Yes, using conduit                   | Yes           | Yes                                       | No                                |
|                                  | Sensor Location     | N/A                  | Integral, Microwave   | Integral                             | N/A           | Integrated                                | Integrated                        |
|                                  | DLC                 | Standard             | DLC, Title 24 Non-Res | DLC Linear, Low-bay Title 24 Non-Res | None          | DLC, Title 24 Res                         | Standard                          |
|                                  | Lumen / CCT Select  | No                   |                       |                                      | No            |   | No                                |
|                                  | Integrated Controls | Basic Occupancy      |                       | ✓                                    | ✓             |   | ✓                                 |
| Stand Alone Daylight / Occupancy |                     |                      |                       | ✓                                    |               | ✓   | ✓                                 |
| WaveLinX LITE                    |                     |                      |                       | ✓                                    |               | ✓   | ✓                                 |
| WaveLinX                         |                     |                      |                       | ✓                                    |               | ✓   | ✓                                 |

Notes: 1. ●●● = high applicability, ●● = medium applicability, ● = low applicability, blank = non-applicable.