

Project		Catalog #		Type	
Prepared by		Notes		Date	




Ephesus

LUMASPORT 16

White LED Sports & Entertainment Luminaire

Typical Applications
Pro Stadiums • University & Collegiate Stadiums

- 
Interactive Menu
- Dimensional Details [page 1](#)
 - Ordering Information [page 2](#)
 - Dimensional and Mounting Details [page 3](#)
 - Performance Data [page 3](#)
 - Electrical and Optical Performance Data [page 4](#)
 - Ordering Information for Accessories [page 5](#)
 - Accessory Dimensions and Part Details [page 6](#)
 - Example System Topology [page 8](#)

Product Certification




Top Product Features


- 158,000 to 199,000 lumen output options
- Glare and cutoff control with three patented and award-winning optical system solutions
- Reduce install time with pre-aimable two-piece assembly
- Virtually eliminate maintenance with power redundancy
- Industry leading light source reliability with Chip-on-Board LEDs
- Greater than 80% lumen maintenance at >66,000
- Wired DMX or Wireless AirMesh controls options to suit your needs
- Options to meet Trade Agreements Act requirements

Dimensional Details

LIGHT HEAD



DRIVER BOX



 **Installation Instructions**

Ordering Information - Luminaire

NOTE: A complete luminaire order requires a selection entry for **Brand, Family, Model, Power, Color, CCT, CRI, Optic, DC Cable, Voltage, Controls, Mount, AC Cable, Options, Packaging, and International Options.**

SAMPLE ORDER NUMBER: **EPH-LS-16-1200L-BLK-57-80-1R-C04-LV-AM-LY-A00-HEG-BP-ST**


Brand	Family	Model	Power	Color	CCT	CRI	Optic	Light Head Cable (DC)
Brand	Family	Model	Power	Color ³	CCT ⁴	CRI	Optic ⁵	Light Head Cable (DC) ⁶
EPH = Ephesus, Standard TAA =Trade Agreements Act ¹	LS = LumaSport	16 = 16 Optics	1200L = 1200W Local Power ²	BLK = Black WHT = White	40 = 4000K 57 = 5700K	70 = 70 CRI 80 = 80 CRI	1R = Reflector: NEMA 2 11 21 2R = Reflector: NEMA 3 16 32 3R = Reflector: NEMA 2 15 27 4R = Reflector: NEMA 3 19 37 5R = Reflector: NEMA 3 25 37 1L = Reflector + Louver: NEMA 2 11 22 3L = Reflector + Louver: NEMA 2 13 27 5L = Reflector + Louver: NEMA 3 20 38 1S = Silicone: NEMA 3 18 34 2S = Silicone: NEMA 3 22 41 3S = Silicone: NEMA 3 27 48 4S = Silicone: NEMA 4 36 67 5S = Silicone: NEMA 5 47 81	C04 = 4ft Cable, Standard C10 = 10ft Cable
Notes: (1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to DOMESTIC PREFERENCES website for more information. Components shipped separately may be separately analyzed under domestic preference requirements.			Notes: (2) Local Power means that the light head is attached to the driver box with the yoke mount.	Notes: (3) Not coastal rated. Contact Ephesus for coastal luminaire options.	Notes: (4) 4000K option is available in 70 CRI only		Notes: (5) Optic = NEMA TYPE; BEAM ANGLE; FIELD ANGLE. Additional optical performance data within spec sheet.	Notes: (6) DC Cable connecting the Light Head to the Driver Box.

Voltage	Controls	Mount	Power Cable (AC)	Options	Packaging	International Options
Voltage	Control	Mount	Power Cable (AC) ⁷	Options ⁸	Packaging	International Options
LV = Low Voltage HV = High Voltage	AM = Wireless AirMesh LB = Wired DMX NC = No Control	LY = Local Yoke	A00 = No Cable, Standard A05 = 5ft Cable A10 = 10ft Cable A15 = 15ft Cable	HEG = No Visor High Efficiency Glass Lens	BP = Bulk Packaging	ST = Standard
:			Notes: (7) AC Cable connecting the Driver Box to the electrical power source.	Notes: (8) Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.		


DesignLights Consortium® Qualified. Refer to www.designlights.org Qualified Products List under Family Models for details

Dimensional and Mounting Details

MOUNTING: DRIVER BOX



MOUNTING CONFIGURATION: LOCAL YOKE



Performance Data¹

	LUMASPORT 16
Lumen Output Range ²	158,000lm to 199,000lm
Nominal Power ³	1290W
Input Voltage (Low Voltage)	208-277VAC
Input Voltage (High Voltage)	347-480VAC
Efficacy Range ²	126 - 160lm/W
CRI ⁴	70, 80
TLCI ³	75
CCT	4000K, 5700K
Distribution (NEMA)	2, 3, 4, 5
Dimming Range	DIM TO OFF, 10%-100%
Operating Temperature Range	-40°C to +40°C
Usage	INDOOR, OUTDOOR ⁵
Mounting Options (1.5G RATED)	LOCAL YOKE
Electrical Certifications	FCC, UL8750, UL1598, DLC Standard (NANQSV)
Environmental Certifications ⁶	ANSI C136.31-2010 1.5G, IP66, NEMA 4X
Surge	10kV
Effective Projected Area (EPA)	2.9 (sq. ft.)
Approximate Weight ⁷	94.5 lbs

NOTES:

- (1) Specifications are subject to change without notice.
- (2) Refer to Optical Performance Data.
- (3) Values are +/- 4% when luminaire is operated at 25°C ambient.
- (4) Values are +/- 2%
- (5) When driver box is mounted in upright position.
- (6) Light head meets NEMA4X Certification
- (7) Weight may vary depending on mounting bracket, light head and driver box selection.

Electrical Performance Data

Product	Input Voltage Range (VAC)	Nominal Input Power (W)	Input Current (A)	Power Factor (>60% Load)	THD (>60% Load)	Inrush (A2s)	Inrush period (ms)	Peak Inrush (A)
LS-16-1200	208-277	1290 (1393 Max)	4.7 - 6.2 (6.2 Max)	> 0.9	< 20%	4.9	7.64	128
	347-480	1290 (1350 Max)	2.8 - 3.7 (4.7 Max)	> 0.9	< 20%	40.8	1.74	360


Ordering Information for Accessories

NOTE: A complete accessory order requires a selection entry for **Brand, Accessory, Option**.

SAMPLE ORDER NUMBER: **EPH-HRDM34-025**

Brand	Accessory	Option	Intended Use
EPH = Ephesus	DVGBRD = Diving Board ¹		Designed to be used with the LUMASPORT 8, LUMASPORT 16 & LUMADAPT 8 luminaires only.
	HRDM34 = Mounting Hardware 3/4in diameter	025 = .25in ² 075 = .75in ² 200 = 2in ²	HRDM34-025: .25-.50in clamping thickness, use for diving board (DVGBRD) or other flat surfaces drilled for 3/4 hardware HRDM34-075: .50-.75in clamping thickness, flat surfaces drilled for 3/4 hardware HRDM34-200: 2.00in clamping thickness, use for 2in x 4in Cross arms that are drilled for 3/4 hardware
	Notes: (1) Additional mounting fastener hardware kit needed to attach a luminaire to the DVGBRD = Diving Board	Notes: (2) Option only available for use with HRDM34	

Diving Board (DVGBRD) Dimension and Part Details:



Diving Board Data

MODEL #	WEIGHT (LBS)
DVGBRD	15.1
DVGBRD + HRDM34-025	16.1

Diving Board Parts

DESCRIPTION	QUANTITY
Welded Bracket	1
Bolt Sleeve	2
3/4in-10 X 6in Structural Hex Bolt, Hot Dip Galvanized	2
3/4in Steel Flat Washer, Hot Dip Galvanized	2
3/4in Ext Tooth Washer, Steel, Magni-565 Grey Polycoat	2
3/4in-10 Structural Steel Hex Nut, Hot Dip Galvanized	2
Stainless Shim	1

HRDM34 Dimension and Part Details:

HRDM34-025:

.25-.50in clamping thickness, use for diving board (DVGBRD) or other flat surfaces drilled for 3/4 hardware

HRDM34-075:



.50-.75in clamping thickness, flat surfaces drilled for 3/4 hardware

HRDM34-200:

2.00in clamping thickness, use for 2inx4in Cross arms that are drilled for 3/4 hardware


HRDM34 Data

MODEL #	WEIGHT (LBS)
HRDM34-025	1
HRDM34-075	1.5
HRDM34-200	2




Example System Topology (Wired DMX Controls)

Example system topology showing the LUMASPORT 16 System in a commonly used wired DMX Control Installation. Refer to the specifications and limitations of your wired DMX control device before installing this configuration.



Example System Topology (Remote Access Point With Wired DMX Controls)

Example system topology showing the LUMASPORT 16 System in a commonly used remote access point with wired DMX Control Installation. Refer to the specifications and limitations of your wired DMX control device before installing this configuration. Note: Laptop and mobile device not included. A cellular network connection requires a cellular carrier network plan.




NOTES:

Remote Access Point requires either a wired internet connection at the lighting system site or through a cellular carrier network connection plan.

Example System Topology (Contactor Controls)

Example system topology showing the LUMASPORT 16 System in a Wired Contactor Controls Installation.

Note: Laptop and mobile device not included. A cellular network connection requires a cellular carrier network plan.



Example System Topology (Wireless AirMesh Controls)

Example system topology showing the LUMASPORT 16 System in a Wireless AirMesh Control Installation.

Note: Laptop and mobile device not included. A cellular network connection requires a cellular carrier network plan.

