

Project		Catalog #		Type	
Prepared by		Notes		Date	



Metalux

Vaportite LED

2' Industrial LED Lamp
Vaportite Industrial Refrigerated Case

Typical Applications

Parking Garage • Cold Storage • Canopy • Warehouse • Food Processing • Manufacturing • Complex Environments

Interactive Menu

- Order Information page 2
- Photometric Data page 2
- Product Warranty

Product Certification




Product Features




Top Product Features

- 2ft, 4ft, and 8ft Sealed and Gasketed Vaportite
- Lumen packages up to 22K lumens
- High-Performance efficacy up to 150 LPW
- LEDs available in 3500K, 4000K and 5000K at 80 CRI
- Rated for -40c to 35c ambient


Dimensional and Mounting Details



Installation Data



MOUNTING BRACKETS
Furnished
Two per 2' and 4' Unit
Four per 8' Unit




OPTIONAL CHAN HANGING SET
(VT2-CHAIN/SET-U)
Includes 6 ft. of chain, 4 large S-Hooks and 4 small S-Hooks
Order One (1) Kit for each 2' or 4' Fixture
Two (2) Kits Recommended For 8' Fixture

Order Information

SAMPLE ORDER NUMBER: **2VT2-LD5-3-DR-UNV-L840-CD1-WL-U**

Series	Lamp Type	LED Lumens Output	Lens	Distribution	Voltage	Remote Emergency Enclosure
Series ^{(1), (2)}	Lamp Type	LED Lumens Output	Lens	Distribution	Voltage	Remote Emergency Enclosure
2VT2=2' Vaportite	LD5=LED 5.0	2=2000 Lumens 3=3000 Lumens 4=4000 Lumens 5=5000 Lumens ⁽³⁾	DR=Internal Prismatic Lens/15% DR High Impact Additive DR100=Internal Prismatic Lens/100% DR High Impact Additive FR50=Frosted Lens/15% DR High Impact Additive ⁽⁴⁾	[Blank]=Medium (Standard) W=Wide Distribution	UNV=Universal Voltage 120-277	VT-REM-EL=Emergency Installed, 700 lumens ⁽⁵⁾
Notes (1) To order product that is compliant with the Buy American Act of 1933 (BAA) or Trade Agreements Act (TAA), use the online specification configurator to specify BAA or TAA. Please refer to DOMESTIC PREFERENCES LINK for more information. (2) DesignLights Consortium® Qualified and classified for both DLC Standard and DLC Premium, refer to www.designlights.org for details.		Notes (3) 2ft, 5000 lumen configuration rated up to 30°C max ambient.	Notes (4) Not available in wide distribution.			Notes (5) EL must specify 120 or 277V only.

Lamps	Driver Type	Label	Options	Packaging	Accessories
Lamps	Driver Type	Label	Options	Packaging	Accessories (order separately)
L835=3500K, LED L840=4000K, LED L850=5000K, LED	CD1=1 Dimming Driver	WL=Wet Location Label	SSL=Stainless Steel Latches TH=(2) Top Watertite Hubs TEH=(2) Top and (2) End Watertite Hubs (all Watertite Hubs have 1/2" Conduit Entry) MS=Damp Listed Motion Sensor MSWL20=Wet Listed Motion Sensor, max 20ft mounting height HBE11=Wet location PIR Indoor/Outdoor Occupancy Sensor ⁽⁶⁾	U=Unit Pack	VT2-Chain/Set-U=Chain Hanging Set. Includes 6 ft. of chain, 4 large S-Hooks and 4 small S-Hooks Order One (1) Kit for each 2' or 4' Fixture VT2-SS-MBK=Stainless Steel Mounting Bracket
			Notes (6) Available for 120V, 277V, and 347V voltage only.		

Product Specifications

Construction

- Rugged and durable construction
- Fiberglass housing is reinforced polyester and self-extinguishing (ASTM-D635-74) plastic
- Full metal fixture liner
- Watertight housing
- 1/2" conduit entry at each end of housing (standard) for continuous feed
- Polyurethane gasketing provides a continuous seamless seal for the diffuser lens
- Four sturdy cam latches clamp diffuser tightly for a positive seal between housing, gasketing and diffuser
- Surface or chain mounting

Electrical

- Long-Life LED system coupled with electrical driver for optimal performance
- LED's available in 3500K, 4000K and 5000K with a CRI ≥ 80
- Projected life is 60,000 hours at 91% lumen output
- Electronic drivers are available for 120-277V applications
- 0-10V dimming control (standard)
- Operating temperature of -40°C to 35°C; Ideal for cold storage environments

Lens

- High-impact diffuser lens
- Internal Prismatic Lens with 15% DR High Impact Additive (DR) or Internal Prismatic Lens with 100% DR High Impact Additive (DR100)
- Frosted Lens with 15% DR High Impact Additive (FR50) option

Finish

- Housing is permanent pearl gray color


Warranty

- Five-year limited warranty


Compliance

- UL/cUL listed for Wet location
- RoHS compliant
- LED modules comply with IESNA LM-79 and LM-80 standards
- NSF listed
- DesignLights Consortium® Qualified and classified for both DLC Standard and DLC Premium (refer to [www.designlights.org](#) for details)
- The VT2 Series ratings apply to Horizontal Mounting only

Photometric Data

 View IES files


2VT2-LD5-4-DR-W-UNV-L840-CD1-WL-U
Electronic Driver
Linear LED 4000K
Spacing criterion: (II) 1.22 x mounting height,
(L) 1.59 x mounting height
Lumens: 3603
Input Watts: 28.9W
Efficacy: 124.7 lm/W
Test Report:
2VT2-LD5-4-DR-W-UNV-L840-CD1-WL-U.IES



2VT2-LD5-4-DR-UNV-L840-CD1-WL-U
Electronic Driver
Linear LED 4000K
Spacing criterion: (II) 1.21 x mounting height,
(L) 1.23 x mounting height
Lumens: 4075
Input Watts: 28.9W
Efficacy: 141 lm/W
Test Report:
2VT2-LD5-4-DR-UNV-L840-CD1-WL-U.IES

Energy and Performance Data

Lumen Maintenance

Ambient Temperature	TM-21 Lumen Maintenance (60,000 hours)	Theoretical L70 (Hours)
25°C	> 91%	> 237,000

Input Watts:

2VT2-LD5-2 (2,000 lumens)=17W
2VT2-LD5-3 (3,000 lumens)=22W
2VT2-LD5-4 (4,000 lumens)=29W
2VT2-LD5-5 (5,000 lumens)=39W

Shipping Data

Catalog No.	Wt.
2VT2-LD5	10 lbs.