

# TK16 & TK32 - TrackKeeper

Catalog#	Prepared by
Project	Date
Comments	Type



## Overview

The TrackKeeper current limiting panel for track lighting allows designers to easily meet energy codes. Limiting the branch circuit volt-ampere rating with the TrackKeeper provides you with a fixed power consumption limit for your installation, as opposed to calculated values based on watts per linear foot of track. Designers can now specify as many linear feet of track as desired without paying a penalty. Additionally, the use of high efficiency luminaires will often yield a lower watts/linear foot number than is specified in the code. Keep your track lighting installation options open with the TrackKeeper.

## Features

- Track light current limiting panel
- Helps your design meet energy codes
- Allows track lighting installations to be based on volt-ampere rating of load instead of track length
- Available in 16 or 32 circuit panels
- Circuit breaker sizes range from 0.5 to 60A
- Surface or flush mount options
- Factory assembled and ready to install
- All breakers use C type curve
- All breakers have UL1077 listing

May 2019

## Specifications


<b>Enclosure</b>	NEMA 1, 14 gauge steel, hinged locking door Surface or flush mount
<b>Surface Size</b>	16 circuit: 10"H X 14"W X 3 3/8"D 32 circuit: 16"H X 14"W X 3 3/8"D
<b>Flush Size</b>	16 circuit: 11 1/2"H X 15 1/2"W X 3 3/8"D 32 circuit: 17 1/2"H X 15 1/2"W X 3 3/8"D
<b>AIC Rating</b>	10,000A, 120 VAC; 6,000A, 277 VAC
<b>Available Circuit Breaker Ratings (A):</b>	0.5, 1, 2, 3, 4, 5, 6, 7, 8, 10, 13, 15, 16, 20, 25, 30, 32, 40, 50, 60 All breakers use C Type curve
<b>Circuit Breaker Wire Size Range</b>	14 to 6 AWG
<b>Operating Environment</b>	Temperature: 23° to 140°F (-5°C to 60°C) Relative Humidity: 0 - 95%, non-condensing
<b>Standards</b>	UL 508A Listed with UL 1077 Listed circuit breakers

## System Includes

- NEMA 1 enclosure
- Hinged locking door
- As many as 16 or 32 circuit breakers

## Ordering

Specify enclosure size, mounting option, voltage and number of circuit breakers desired.



Example: TK16-120-14-F specifies a 16 circuit flush mount enclosure with 15 120V circuit breakers.

**Cooper Lighting Solutions**  
 1121 Highway 74 South  
 Peachtree City, GA 30269  
 P: 770-486-4800  
[www.cooperlighting.com](http://www.cooperlighting.com)  
 For service or technical assistance:  
 1-800-553-3879

© 2020 Cooper Lighting Solutions  
 All Rights Reserved  
 Printed in USA  
 Publication No. TD503188EN  
 May 2019

Specifications and  
 dimensions subject to  
 change without notice.