


Project		Catalog #		Type	
Prepared by		Notes		Date	



Metalux

Encounter 24EN LED

2' x 4' Troffer LED Module
Specification Grade Troffer

Typical Applications

- Commercial Office Spaces • Schools • Hospitals • Retail
- Other Indoor Ambient Applications

Product Certification



Product Features






Interactive Menu

- Order Information page 2
- Photometric Data page 3
- Control Solutions page 4
- Product Warranty


Top Product Features

- Available in 1' x 2', 1' x 4', 2' x 2' and 2' x 4' recessed versions
- Leverages our patented WaveStream Technology with AccuAim™ optics
- Four CCT options: 3000K, 3500K, 4000K, and 5000K at 80CRI or 90 CRI
- White tuning solutions available, either 3000K - 5000K or 2700K - 6500K
- Efficacy up to 143 lumens per watt
- Options to meet Build America, Buy America, Buy American and other domestic preference requirements

Dimensional and Mounting Details



Ceiling Compatibility



Notes:

- *See Drywall Frame Kit Accessory in Ordering Information section.
- **Fixture construction is suitable for use in Air-handling and plenum rated spaces in accordance with Section 300.22 (C) of the National Electrical Code, Section 4.3.11.2.6.5 of NFPA 90A and Section 602.2.1.4 of ICC.

Order Information

SAMPLE ORDER NUMBER: 24EN-LD2-67-UNV-L835-CD1-WPN-U

--	--	--	--	--	--

Domestic Preferences ⁽¹⁾	Rating	Series ⁽³⁾	Air	Lamp Type	Lumen Outputs	Voltage ⁽⁷⁾
[Blank]=Standard BAA=Buy American Act TAA=Trade Agreements Act BABA=FWHA and FTA projects funded through October 1, 2026	[Blank]=Standard ATW-SW4=Chicago Rated ⁽²⁾	24EN=2' x 4' Encounter Series	[Blank]=Standard A=Air (Vented) ⁽⁴⁾	LD2=LED 2.0	Stock 45=4500 Lumens 54=5400 Lumens 67=6700 Lumens MTO 30=3000 Lumens ^{(5), (6)} 34=3400 Lumens ^{(5), (6)} 40=4000 Lumens 49=4900 Lumens 58=5800 Lumens 70=7000 Lumens ⁽⁵⁾ 74=7400 Lumens ⁽⁵⁾	UNV=Universal Voltage 120-277 347V=347 Volt ⁽⁸⁾ 120V=120 Volt ⁽⁹⁾ 277V=277 Volt ⁽⁹⁾
Notes (1) Only product configurations with these prefixes are built to be compliant with the Buy American Act of 1933 (BAA), Trade Agreements Act of 1979 (TAA), or the Build America Buy America Act (BABAA). BABAA is the minimum Government compliance requirement for the Build America Buy America standards which is part of the Infrastructure and Investment Jobs Act (IIJA). Individual Government Agencies may have more stringent compliance standards. BABAF designates the product will meet the standards set for FHWA and FTA. As noted, these must be funded by October 1, 2026. Please refer to DOMESTIC PREFERENCES website or consult the CLS Domestic Preferences team for more information. Components shipped separately may be separately analyzed under domestic preference requirements.	Notes (2) Chicago rated version does not allow for row mounting.	Notes (3) DesignLights Consortium® Qualified and classified for both DLC Standard and DLC Premium, refer to www.designlights.org for details.	Notes (4) Air version is vented but does not meet air handling requirements.		Notes (5) Step-dim driver not available with 3000, 3400, 7000 and 7400 lumen options. (6) SLTD DALI option not available with 3000 and 3400 lumen packages. (7) Products also available in non-US voltages and frequencies for international markets. (8) 347V emergency option not available. (9) Must specify voltage as 120V or 277V when ordering GTR2 option.	Notes

Emergency Optionsx	CCT	Flex	Driver Type
EL7W=7-watt 120V-277V emergency battery pack ⁽¹⁰⁾ EL10W=10-watt 120V-277V emergency battery pack ⁽¹⁰⁾ EL14W=14-watt 120V-277V emergency battery pack ⁽¹⁰⁾ EL10WSD=10W emergency battery pack with self-diagnostic installed ^{(10), (13)} EL14WSD=14W emergency battery pack with self-diagnostic installed ^{(10), (13)} GTR2=Bodine Generator Transfer Relay ^{(11), (12)} ETRD=Emergency Transfer Relay with dimming control ⁽¹¹⁾	L830=3000K L835=3500K L840=4000K L850=5000K L930=3000K L935=3500K L940=4000K L950=5000K L83050=80CRI 3000K-5000K White Tuning ⁽¹⁴⁾ L93050=90CRI 3000K-5000K White Tuning ⁽¹⁴⁾ L82765=80CRI 2700K-6500K White Tuning ⁽¹⁴⁾ L92765=90CRI 2700K-6500K White Tuning ⁽¹⁴⁾	A3/8-4/18GDIM=3/8" Flex with 0-10V Dimming Leads Multiple other configurations available. See below for details. A3/8-5/18GDIM=Flex with 0-10V Dimming leads and Blue for alternate wiring. See below for details.	CD=0-10V Driver (1%-100% Dimming) SLTD=DALI Driver (5%-100% Dimming) ⁽¹⁷⁾ SLTHD=DALI Driver (1%-100% Dimming) ⁽¹⁶⁾ SD=Step Dimming Driver (50% or 100% Dimming) ⁽¹⁵⁾ LH=Lutron HiLuma (LDE1 series) 1%-100% EcoSystem Driver with Soft-on/Fade to Black dimming ⁽⁷⁾ W2A=White Tuning, 2ch, Intensity and CCT Control ⁽¹⁸⁾ SR=Sensor-ready Driver (1%-100% Dimming)
Notes (10) Factory installed with integral test switch/indicator/laser test. For approximate delivered lumens multiply the lumens per watt of the desired fixture by the wattage of the emergency battery pack (100 lm/W x 7=700 lumens). IES-format photometry for luminaire under emergency operation available. Battery option increases total height by 1 inch. (11) Used to bypass local control during outage. Must be used in conjunction with UL 1008 device (provided by others). GTR2 option includes 2 relays on fixtures with dimming drivers. ETRD option only requires one relay when used on a dimming fixture. (12) Must specify voltage as 120V or 277V when ordering GTR2 option. (13) EL10WSD and EL14WSD not available with 347V.	Notes (14) White tuning provides correlated color temperatures (CCT) between 3000K (warm) to 5000K (cool) or 2700K (warm) to 6500K (cool). Must be used in conjunction with W2A driver only. Must be used with two (2) 10V dimming control channels, 1 color, 1 intensity.	Flexible Metal Conduit Options Flex options available for 0-10V dimming control, DALI dimming control, emergency and night light functions. 72-inch factory-staffed and pre-wired to driver, fitted to luminaire housing access plate with 90° enclosed FMC connector. Not all options may be combined and installation ratings vary by type. A3/8-4/18GDIM series notes: Factory installed dimming option 3/8" flexible metal conduit with 2#18 power and ground wires and 2#18 UL-listed jacketed 0-10V +/- control wires. Meets UL 66, 83, 1479, 1569, 1581, 2556, NEC® 250.118, 300.22(C), 392, 396, 330, 501, 502, 503, 530, 504, 505, 518, 520, 530, 645, 72; Federal Specification A-A-59544 (formerly J-C-30B); all applicable OSHA and HUD Requirements. UL Classified 1, 2, and 3-hour through penetration with applicable fire stop product (not included). May be surface mounted, fished and/or embedded in plaster. Cable tray and approved raceway rated, install per NEC®. Environmental Air-Handling Space Installation per NEC® 300.22(O).	Notes (15) Step-dim (SD) driver not available with 3000, 3400, 7000 and 7400 lumen options. (16) Two drivers required for DALI (SLTHD) option for 6700 lumens and up. (17) DALI (SLTD) option not available with 3000 and 3400 lumen packages. (18) White tuning provides correlated color temperatures (CCT) between 3000K (warm) to 5000K (cool) or 2700K (warm) to 6500K (cool). Must be used in conjunction with W2A driver only. Must be used with two (2) 10V dimming control channels, 1 color, 1 intensity. Integrated options must be used in conjunction with the associated system and may not be compatible with other options or accessories. Please refer to the following: (F) Consult Marketplace Options - Lutron system pages for additional details and compatibility. Compatible only with driver series shown, and may require two or more drivers. Requires field commissioning to operate or dim. Contact Lutron at www.lutron.com .

Number of Drivers	Integrated Sensing Systems	Packaging	Accessories (order separately) ⁽²¹⁾
1=1 Driver 2=2 Drivers	[Blank]=No Sensor WLS (formerly WAB)=WaveLinx LITE Wireless Sensor, Occupancy w/ photocell, Independent & Networked ^{(20), (8)} WPS (formerly WAA)=WaveLinx PRO Wireless Sensor, Occupancy w/ photocell, Networked ^{(19), (A)} WLN=WaveLinx LITE Wireless Control Node, without sensor ^{(20), (8)} WPN=WaveLinx PRO Wireless Control Node, without sensor ^{(19), (A)}	U=Unit Pack PALC=Job Pack, in carton	T3A END E.Q. BRACKET PARTS BAG (Standard with fixture) DF-24W-U=2' x 4' Drywall Frame Kit SMK-24-W=2' x 4' Shallow Surface Mount Kit SK-24-WT=4" Tall Surface Mount Kit, 2' x 4'
	Notes (19) WPS sensor and WPN node to be used with CD or W2A driver. Consult factory for WPN with tunable white W2A driver. (20) WAB sensor and WLN node to be used with CD driver. Integrated options must be used in conjunction with the associated system and may not be compatible with other options or accessories. Please refer to the following: (A) Consult WaveLinx PRO system pages for additional details and compatibility. (B) Consult WaveLinx LITE system pages for additional details and compatibility.		Notes (21) Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information. Integrated options must be used in conjunction with the associated system and may not be compatible with other options or accessories.

Product Specifications

Construction

- Shallow 3-1/16" deep housing extruded aluminum frame
- Injected molded composite end plates
- End plates screws for strength, rigidity and gap eliminations
- End plates accessory grid-lock feature adds safety
- Four auxiliary fixture end suspension points
- Large access plate for supply connection


Controls

- 0-10V dimming to 1% standard
- Integrated WaveLinx options provide wireless individual fixture control and enable code compliance, increased energy savings, grouping of fixtures, and connection to WaveLinx control systems
- DALI 2.0, Lutron, and step-dimming available


Electrical

- LED's available in 3000K, 3500K, or 4000K at 80 CRI or 90 CRI minimum
- Color accuracy ≤ 3 -Step MacAdam ellipse (SDCM)
- TM21 life at 60,000 hours up to L92 and calculated L70 exceeds 288,000 hrs
- Drivers available in 120-277V and 347V
- Tunable white options available with Cooper Lighting's VividTune

Photometric Data



24EN-LD2-45-UNV-L835-CD1-U
 Electronic Driver
 Linear LED 3500K
 Spacing criterion: (II) 1.29 x mounting height,
 (L) 1.29 x mounting height
 Lumens: 4656
 Input Watts: 38W
 Efficacy: 122.5 lm/W
 Test Report: 24EN-LD2-45-UNV-L835-CD1-U.IES



24EN-LD2-54-UNV-L835-CD1-U
 Electronic Driver
 Linear LED 3500K
 Spacing criterion: (II) 1.3 x mounting height,
 (L) 1.3 x mounting height
 Lumens: 5410
 Input Watts: 43.0W
 Efficacy: 125.8 lm/W
 Test Report: 24EN-LD2-54-UNV-L835-CD1-U.IES

 View IES files

Energy and Performance Data

Stock or MTO	Catalog Logic	Delivered Lumens	Watts	Efficacy (LPW)
MTO	24EN-LD2-30-UNV-L835-CD1-U	3117	24.6	127
MTO	24EN-LD2-34-UNV-L835-CD1-U	3610	28.7	126
MTO	24EN-LD2-40-UNV-L835-CD1-U	4204	33.9	124
STOCK	24EN-LD2-45-UNV-L835-CD1-U	4656	38.0	123
STOCK	24EN-LD2-45-UNV-L840-CD1-U	4748	38.0	125
MTO	24EN-LD2-49-UNV-L835-CD1-U	5099	42.2	121
STOCK	24EN-LD2-54-UNV-L835-CD1-U	5410	43.0	126
STOCK	24EN-LD2-54-UNV-L840-CD1-U	5518	43.0	128
MTO	24EN-LD2-58-UNV-L835-CD1-U	5838	47.0	124
STOCK	24EN-LD2-67-UNV-L835-CD1-U	6731	56.1	120
STOCK	24EN-LD2-67-UNV-L840-CD1-U	6866	56.1	122
MTO	24EN-LD2-70-UNV-L835-CD1-U	7023	60.2	117
MTO	24EN-LD2-74-UNV-L835-CD1-U	7484	63.6	118

Shipping Data

Catalog No.	Weight (lbs)	Units per Pallet 49" L x 52" W x 55" H
24EN-LD2	28	18

Lumen Maintenance

Ambient Temperature	TM-21 Lumen Maintenance (60,000 hours) ⁽¹⁾	Theoretical L70 (Hours) ⁽²⁾
25°C	> 92%	> 288,000

Notes: (1) Supported by IES TM-21 standards. (2) Theoretical values represent estimations commonly used; however, refer to the IES position on LED Product Lifetime Prediction, IES PS-10-18, that explains proper use of IES TM-21 and LM-80.

Lumen Calculator

CCT Multiplier	80 CRI	90 CRI
3000K	0.970	0.835
3500K	1.000	0.864
4000K	1.020	0.901
5000K	1.110	0.955

Example of Lumen Adjustment Calculation

24EN-LD2-45-UNV-L835-CD1-U
 at 90CRI at 3500K

Lumen Adjustment Factor = 0.864

Total Light Output = 4,651 lm x 0.864 = 4,022 lm

Efficacy = $\frac{4,022 \text{ lm}}{38\text{W}} = 105.8 \text{ lm/W}$


Control Solutions

- WaveLinx LITE wireless
- WaveLinx PRO wireless
- WaveLinx CAT wired
- WaveLinx Wired




Integrated Sensor Coverage Pattern


TOP VIEW:




SIDE VIEW:



With Integrated WaveLinx Sensor



With Integrated WaveLinx Node



Add a hidden WaveLinx sensor node (WPN, WLN) to your space lighting design!

Allows to:

- Keeps luminaire aesthetics
- Connect fixtures without the realestate to include sensor option such as downlights
- Connect sealed fixtures without a standard sensor option such as products for clinical space.

Note: Installation of integrated sensors within 3-ft (1m) of HVAC air vents is not recommended. The pattern shown is intended solely as a general guide and is not to scale.

The Encounter with WaveLinx offers no-hassle lighting control with multiple luminaire level control solutions.



WaveLinx PRO is a wireless lighting control solution, for connected spaces, that significantly reduces a building's energy consumption. From a single floor to an entire campus, WaveLinx PRO connects more than lighting assets; it shares aggregated sensor data with the WaveLinx CORE platform and other building systems, so building owners can improve operations, spaces environment, and tenants' experience. WaveLinx PRO offers a rich portfolio of wireless devices, WaveLinx PRO-enabled luminaires, and an intuitive WaveLinx mobile app for office, education, warehouse, and parking garage applications.



WaveLinx LITE is a cost effective, wireless digital lighting control solution, with out-of-the-box functionality, that saves energy and meets code. It's designed for applications that require occupancy-based, daylighting, or manual light control. Customize installations for office, education, warehouse and parking garages using the secure, simple mobile app.

Integrated Controls Options

Option	Out of the Box Functionality	Luminaire Level Lighting Control (LLLC)	Automatic Dimming Photocell	Occupancy Sensing	CCT Control*
WLS	X	X	X	X	
WLN		X			
WPS		X	X	X	X
WPN		X			X

Note: *WaveLinx utilizes scenes to allow users to change an area's fixtures Correlated Color Temperature (CCT) and intensity using a commissioned wireless wallstation scene controller. To enable CCT adjustments through WaveLinx, include WPS or WPN devices in addition to VividTune or BioUp technologies for integrated fixture control. WPS with CCT controls the intensity of the fixture; an additional, externally mounted control device is needed to control the CCT. See [RSP-P-010-347](#)

The WNPS option is available with WLS or WPS sensors. Must be specified when ordered. Also note that WLS and WPS are also compatible with ESP-L-010-347 and ESP-P-010-347, respectively. Learn more about WaveLinx EM [here](#).

Systems comparison chart

Cooper Lighting Solutions provides many lighting system solutions designed to satisfy code requirements and meet the unique needs of any project.



Luminaire with standalone sensor



Standalone Spaces
WaveLinx LITE



Standalone Spaces
WaveLinx CAT



Networked Spaces
WaveLinx PRO




Enterprise WaveLinx CORE

Occupancy	Yes	Yes	Yes	Yes	Yes
Daylighting	Yes	Yes	Yes	Yes	Yes
Wallstations	–	Yes	Yes	Yes	Yes
Gateways	–	–	–	1 WAC	300 WACs
Devices (MAX)	–	40 per Area (1120 per space)	40 per Area	200 per WAC2	32,500 per CORE Enterprise
Software	–	WaveLinx LITE Mobile App	WaveLinx CAT Mobile App	WaveLinx Mobile App	CORE
Areas	–	28 per Space	Unlimited	50 per WAC2	up to 3,000
Zones	–	16 per Area	16 per Area	16 per Area	up to 9,000
Scheduling	–	–	–	Local	Global
VividTune™	–	–	–	Yes	Yes
Plug-Load Control	–	Yes	Yes	Yes	Yes
Low-Voltage Power	–	–	Yes	Yes	Yes
Integration	–	–	–	–	BACnet, API
Dashboards	–	–	–	–	Energy, Occupancy
Configuration	–	Installer	Installer	Technician	Technician / IT



24EN LED with VividTune Tunable White

VividTune tunable white luminaires from Cooper Lighting Solutions deliver high-quality light in a broad range of continuously variable color temperatures and intensities. Create a dynamic environment by adjusting the ambient light warmer or cooler to influence mood, support the task at hand, or create a dramatic ambience. The ability to control correlated color temperature and intensity separately using simple controls is the next evolution of LED lighting for the commercial, educational, healthcare and hospitality space. The unparalleled flexibility and number of available lighting environments enable users to find the right light with tunable white.




Performance Data*

Tunable White - Lumen Adjustment Factors (example only)				
CCT	3000K-5000K		2700K-6500K	
	80 CRI	90 CRI	80 CRI	90 CRI
2700K	-	-	0.894	0.738
3000K	0.968	0.809	0.903	0.762
3500K	0.984	0.827	0.932	0.779
4000K	0.988	0.860	0.919	0.814
4500K	1.002	0.864	0.946	0.808
5000K	1.003	0.868	0.945	0.829
6500K	-	-	0.949	0.850

2' x 4' Encounter LED - Example of Approximate Lumen Calculation			
	Standard Catalog #	VividTune 80 CRI Catalog #	VividTune 90 CRI Catalog #
CCT Setting	24EN-LD2-45-UNV-L835-CD1-U	24EN-LD2-45-UNV-L83050-W2A1-U	24EN-LD2-45-UNV-L93050-W2A1-U
3000K	-	4508	3765
3500K	4656	4582	3853
4000K	-	4601	4002
4500K	-	4663	4023
5000K	-	4668	4042

Controlling VividTune Tunable White

VividTune luminaires make tunable white more accessible by using simple and familiar controls. From wall dimmers to wireless controls, VividTune tunable white luminaires are compatible with industry standard 0-10V dimming controls. A single 0-10V dimming input is used to control intensity (brightness) while a second 0-10V dimming input is used to adjust CCT. For suggested control configurations, [click here](#) for tunable white application guides.



Example of Lumen Adjustment Calculation

24EN-LD2-45-UNV-L83050-W2A1-U
at 80 CRI tuned to 3500K

Adjusted Lumen =
published lm x adjusted lm factor

Adjusted Lumen = 4656 * 0.984

Adjusted Lumen = 4582 lm

* Lumen adjustment factors are for reference
and may be different for each product selected.
Refer to IES files for actual performance data on each.