

Project		Catalog #		Type	
Prepared by		Notes		Date	



## Lumark

### Prevail LED

Area / Site Luminaire

#### Product Features



#### Interactive Menu

- Ordering Information page 2
- Mounting Details page 3, 4
- Optical Configurations page 5
- Product Specifications page 5
- Energy and Performance Data page 6, 7
- Control Options page 8

#### Product Certifications




#### Quick Facts

- Lumen packages range from 4,800 - 84,000 lumens (35W - 588W)
- Replaces 70W up to 1,000W HID equivalents
- Efficacies up to 160 lumens per watt
- Energy and maintenance savings up to 85% versus HID solutions
- Standard universal quick mount arm with universal drill pattern

#### Connected Systems

- WaveLinx PRO Wireless
- WaveLinx LITE Wireless

#### Dimensional Details



**NOTES:**  
1. Visit <https://www.designlights.org/search/> to confirm qualification. Not all product variations are DLC qualified.  
2. IDA Certified for 3000K CCT and warmer only.

## Ordering Information

SAMPLE NUMBER: PRV-XL-C75-D-UNV-T4-SA-BZ


Product Family <sup>1,2</sup>	Light Engine <sup>4</sup>	Color Temperature	Driver	Voltage	Distribution	Mounting	Color
<b>PRV-P</b> =Prevail Petite <b>BAA-PRV-P</b> =Prevail Petite BAA Compliant <sup>3</sup> <b>TAA-PRV-P</b> =Prevail Petite TAA Compliant <sup>3</sup> <b>BABA-PRV-P</b> =Prevail Petite BABA Build America Buy America Act Compliant <sup>30</sup>	<b>C10</b> =(1 LED) 4,900 Nominal Lumens <b>C15</b> =(1 LED) 6,900 Nominal Lumens <b>C20</b> =(1 LED) 9,800 Nominal Lumens <b>C25</b> =(1 LED) 11,800 Nominal Lumens	<b>740</b> =70CRI, 4000K <b>727</b> =70CRI, 2700K <b>730</b> =70CRI, 3000K <b>750</b> =70CRI, 5000K <b>8540</b> =85CRI, 4000K	<b>D</b> =Dimming (0-10V)	<b>UNV</b> =Universal (120-277V) <b>H</b> =High Voltage, 347-480V <b>8</b> =480V <sup>5</sup> <b>9</b> =347V <b>DV</b> =DuraVolt (277-480V) <sup>5,6</sup>	<b>T2</b> =Type II <b>T3</b> =Type III <b>T4</b> =Type IV <b>T5</b> =Type V	<b>SA</b> =QM Standard Versatile Arm <b>MA</b> =QM Mast Arm <b>FMA</b> = Fixed Mast Arm <sup>26</sup> <b>WM</b> =QM Wall Mount Arm <b>ADJA-WM</b> =Adjustable Arm-Wall Mount <sup>28</sup> <b>ADJA</b> =Adjustable Arm-Pole Mount <sup>28</sup> <b>ADJS</b> =Adjustable Arm-Slipfitter, 3" vertical tenon <sup>28</sup> <b>SP2</b> =Adjustable Arm-Slipfitter, 2 3/8" vertical tenon <sup>26,28</sup>	<b>BZ</b> =Bronze <b>AP</b> =Grey <b>BK</b> =Black <b>DP</b> =Dark Platinum <b>GM</b> =Graphite Metallic <b>WH</b> =White
<b>PRV</b> =Prevail <b>BAA-PRV</b> =Prevail BAA Compliant <sup>3</sup> <b>TAA-PRV</b> =Prevail TAA Compliant <sup>3</sup> <b>BABA-PRV</b> =Prevail BABA Build America Buy America Act Compliant <sup>30</sup>	<b>C15</b> =(1 LED) 7,100 Nominal Lumens <b>C25</b> =(2 LEDs) 13,100 Nominal Lumens <b>C40</b> =(2 LEDs) 17,100 Nominal Lumens <b>C60</b> =(2 LEDs) 20,000 Nominal Lumens						
<b>PRV-XL</b> =Prevail XL <b>BAA-PRV-XL</b> =Prevail XL BAA Compliant <sup>3</sup> <b>TAA-PRV-XL</b> =Prevail XL TAA Compliant <sup>3</sup> <b>BABA-PRV-XL</b> =Prevail XL BABA Build America Buy America Act Compliant <sup>30</sup>	<b>C75</b> =(4 LED) 26,100 Nominal Lumens <b>C100</b> =(4 LED) 31,000 Nominal Lumens <b>C125</b> =(4 LED) 36,000 Nominal Lumens <b>C150</b> =(6 LED) 41,100 Nominal Lumens <b>C175</b> =(6 LED) 48,600 Nominal Lumens						
<b>PRV-M</b> =Prevail Maxx <b>BAA-PRV-M</b> =Prevail Maxx BAA Compliant <sup>3</sup> <b>TAA-PRV-M</b> =Prevail MaxxTAA Compliant <sup>3</sup> <b>BABA-PRV-M</b> =Prevail Maxx BABA Build America Buy America Act Compliant <sup>30</sup>	<b>C200</b> =(9 LED) 48,000 Nominal Lumens <b>C225</b> =(9 LED) 56,000 Nominal Lumens <b>C250</b> =(9 LED) 65,000 Nominal Lumens <b>C275</b> =(9 LED) 73,000 Nominal Lumens						
Options (Add as Suffix)			Accessories (Order Separately) <sup>20,21</sup>				
<b>CC</b> =Coastal Construction finish <sup>9</sup> <b>HSS</b> =House Side Shield <sup>7</sup> <b>L90</b> =Optics Rotated 90° Left <b>R90</b> =Optics Rotated 90° Right <b>10K</b> =10kV/10kA UL 1449 Fused Surge Protective Device <b>20MSP</b> =20kV MOV Surge Protective Device <b>20K</b> =20kV UL 1449 Fused Surge Protective Device <b>HA</b> =50°C High Ambient Temperature <sup>8</sup> <b>PR</b> =NEMA 3-PIN Twistlock Photocontrol Receptacle <sup>10</sup> <b>PR7</b> =NEMA 7-PIN Twistlock Photocontrol Receptacle <sup>10</sup> <b>FADC</b> =Field Adjustable Dimming Controller <sup>29</sup> <b>MS/DIM-L08</b> =Dimming Motion and Daylight Sensor, IR Remote Programmable, < 8' Mounting Height <sup>11,12</sup> <b>MS/DIM-L20</b> =Dimming Motion and Daylight Sensor, IR Remote Programmable, 8' - 20' Mounting Height <sup>11,12</sup> <b>MS/DIM-L40</b> =Dimming Motion and Daylight Sensor, IR Remote Programmable, 21' - 40' Mounting <sup>11,12</sup>	<b>SPB1</b> =Dimming Motion and Daylight Sensor, Bluetooth Programmable, < 8' Mounting Height <sup>11,13</sup> <b>SPB2</b> =Dimming Motion and Daylight Sensor, Bluetooth Programmable, 8' - 20' Mounting Height <sup>11,13</sup> <b>SPB4</b> =Dimming Motion and Daylight Sensor, Bluetooth Programmable, 21' - 40' Mounting Height <sup>11,13,26,27</sup> <b>WPS2XX</b> =WaveLinX Pro, SR Driver, Dimming Motion and Daylight, WAC Programmable, 7' - 15' Mounting <sup>11,14,15,16</sup> <b>WPS4XX</b> =WaveLinX Pro, SR Driver, Dimming Motion and Daylight, WAC Programmable, 15' - 40' Mounting <sup>11,14,15,16</sup> <b>WLS2XX</b> =WaveLinX Lite, SR Driver, Dimming Motion and Daylight, Bluetooth Programmable, 7' - 15' Mounting <sup>11,14,15,16</sup> <b>WLS4XX</b> =WaveLinX Lite, SR Driver, Dimming Motion and Daylight, Bluetooth Programmable, 15' - 40' Mounting <sup>11,14,15,16</sup>	<b>PRVSA-XX</b> =Standard Arm Mounting Kit <sup>21</sup> <b>PRVMA-XX</b> =Mast Arm Mounting Kit <sup>21</sup> <b>PRVWM-XX</b> =Wall Mount Kit <sup>21</sup> <b>PRV-ADJA-XX</b> =Adjustable Arm - Pole Mount Kit <sup>21</sup> <b>PRV-ADJS-XX</b> =Adjustable Arm - Slipfitter Kit <sup>21</sup> <b>PRV-ADJA-WM-XX</b> =Adjustable Arm - Wall Mount Kit <sup>21</sup> <b>PRVXLSA-XX</b> =Standard Arm Mounting Kit <sup>27</sup> <b>PRVXLMA-XX</b> =Mast Arm Mounting Kit <sup>27</sup> <b>PRVXLWM-XX</b> =Wall Mount Kit <sup>27</sup> <b>PRV-XL-ADJA-XX</b> =Adjustable Arm - Pole Mount Kit <sup>27</sup> <b>PRV-XL-ADJS-XX</b> =Adjustable Arm - Slipfitter Kit <sup>27</sup> <b>PRV-XL-ADJA-WM-XX</b> =Adjustable Arm - Wall Mount Kit <sup>27</sup> <b>PRV-M-ADJA-XX</b> =Adjustable Arm - Pole Mount Kit <sup>26</sup> <b>PRV-M-ADJS-XX</b> =Adjustable Arm - Slipfitter Kit <sup>26</sup> <b>PRV-M-ADJA-WM-XX</b> =Adjustable Arm - Wall Mount Kit <sup>26</sup> <b>MA1010-XX</b> =Single Tenon Adapter for 3-1/2" O.D. Tenon			<b>MA1011-XX</b> =2@180° Tenon Adapter for 3-1/2" O.D. Tenon <b>MA1017-XX</b> =Single Tenon Adapter for 2-3/8" O.D. Tenon <b>MA1018-XX</b> =2@180° Tenon Adapter for 2-3/8" O.D. Tenon <b>SRA238</b> =Tenon Adapter from 3" to 2-3/8" <b>PRV/COB-FDV</b> =Full Drop Visor <sup>22</sup> <b>PRVXL/COB-FDV</b> =Full Drop Visor <sup>17</sup> <b>HS/VERD</b> =House Side Shield Kit <sup>7,23</sup> <b>VGS-F/B</b> = Vertical Glare Shield Kit, Front/Back <sup>23</sup> <b>VGS-SIDE</b> =Vertical Glare Shield Kit, Side <sup>23</sup> <b>OA/RA1013</b> =Photocontrol Shorting Cap <b>OA/RA1014</b> =NEMA Photocontrol - 120V <b>OA/RA1016</b> =NEMA Photocontrol - Multi-Tap 105-285V <b>OA/RA1201</b> =NEMA Photocontrol - 347V <b>OA/RA1027</b> =NEMA Photocontrol - 480V <b>FSIR-100</b> =Wireless Configuration Tool for Occupancy Sensor <sup>24</sup> <b>WOLC-7P-10A</b> =WaveLinX Outdoor Control Module (7-PIN) <sup>25</sup>		
<b>NOTES:</b> 1. DesignLights Consortium® Qualified. Refer to <a href="http://www.designlights.org">www.designlights.org</a> Qualified Products List under Family Models for details. 2. Customer is responsible for engineering analysis to confirm pole and fixture compatibility for all applications. Refer to installation instructions I8500002EN and pole white paper WP513001EN for additional support information. 3. Only product configurations with these designated prefixes are built to be compliant with the Buy American Act of 1933 (BAA) or Trade Agreements Act of 1979 (TAA), respectively. Please refer to <a href="http://www.designlights.org">DOMESTIC PREFERENCES</a> website for more information. Components shipped separately may be separately analyzed under domestic preference requirements. 4. Standard 4000K CCT and 70CRI. 5. 480V not to be used with ungrounded or impedance grounded systems. 6. DuraVolt drivers feature added protection from power quality issues such as loss of neutral, transients and voltage fluctuations. Visit <a href="http://www.signify.com/duravolt">www.signify.com/duravolt</a> for more information. 7. House Side Shield not suitable with T5 distribution. Not available with PRV-C60 lumen package. 8. Not available with PRV-C60 lumen package. Not available with PRV-P-C25 lumen package. 9. Coastal construction finish salt spray tested to over 5,000-hours per ASTM B117, with a scribe rating of 9 per ASTM D1654. 10. If DuraVolt (DV) is specified, use a photocontrol that matches the input voltage used. 11. Controls system is not available in combination with a photocontrol receptacle (PR & PER7) or another controls system (MS or SPB). Option not available with DuraVolt (DV) voltage option. 12. Utilizes the Wattstopper sensor FSP-211. Sensor color white unless specified otherwise via PDR. To field-configure, order FSIR-100 accessory separately. 13. Utilizes the Wattstopper sensor FSP-3XX series. Sensor color determined by product finish. See Sensor Color Reference Table. Field-configures via mobile application. See Controls section for details. 14. Sensor passive infrared (PIR) may be overly sensitive when operating below -20°C (-4°F). 15. For the device to be field-configurable, requires WAC Gateway components WAC-PoE and WPOE-120 in appropriate quantities. Only compatible with WaveLinX system and software and requires system components to be installed for operation. See website for more WaveLinX application information.			16. Replace XX with sensor color (WH, BZ, or BK). 17. Only available in PRV-XL configurations C75, C100, C125, C150, or C175. 18. Not available with 347V, 480V, DV, or HA options. 19. Replace XX with paint color. 20. For BAA or TAA requirements, Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information. 21. Not for use with PRV-XL or PRV-M configurations. 22. Only for use with PRV. Not applicable to PRV-M, PRV-XL, or PRV-P. 23. Must order one per optic/LED when ordering as a field-installable accessory (1, 2, 4, 6 or 9). 24. This tool enables adjustment to Motion Sensor (MS) parameters including high and low modes, sensitivity, time delay, cutoff and more. Consult your lighting representative for more information. 25. Requires 7-PIN NEMA twistlock photocontrol receptacle (PR & PER7) option. The WOLC-7 cannot be used in conjunction with other controls systems (MS or LWR). Operates on 120-347V input voltages. 26. Only for use with PRV-M configurations. 27. Only for use with PRV-XL configurations. 28. Fixed for PRV-M. 29. Cannot be used with PR7 or other motion response control options 30. Only product configurations with these prefixes are built to be compliant with the Buy American Act of 1933 (BAA) or the Build America Buy America Act (BABA). BABA is the minimum Government compliance requirement for the Build America Buy America standards which is part of the Infrastructure and Investment Jobs Act (IIJA). Individual Government Agencies may have more stringent compliance standards. Please refer to the <a href="http://www.designlights.org">DOMESTIC PREFERENCES</a> website or consult the CLS Domestic Preferences team for more information. Components shipped separately may be separately analyzed under domestic preference requirements.				

## Stock Ordering Information


Product Family <sup>1</sup>	Light Engine	Voltage	Distribution
PRVS=Prevail	C15=(1 LED) 7,100 Nominal Lumens C25=(2 LEDs) 13,100 Nominal Lumens C40=(2 LEDs) 17,100 Nominal Lumens C60=(2 LEDs) 20,000 Nominal Lumens	UNV=Universal (120-277V) 347=347V <sup>2</sup>	T3=Type III T4=Type IV
PRVS-XL=Prevail XL	C75=(4 LED) 26,100 Nominal Lumens C100=(4 LED) 31,000 Nominal Lumens C125=(4 LED) 36,000 Nominal Lumens C150=(6 LED) 41,100 Nominal Lumens C175=(6 LED) 48,600 Nominal Lumens		
NOTES: 1. All stock configurations are standard 4000K/70CRI, bronze finish, and include the standard versatile mounting arm. 2. Only available in PRVS configurations C15, C25, C40 or C60.			

## Mounting Details


**SA=QM Pole Mount Arm (PRV & PRV-P)**




**SA=QM Pole Mount Arm (PRV-XL)**




**WM=QM Wall Mount Arm (PRV & PRV-P)**




**WM=QM Wall Mount Arm (PRV-XL)**




**MA=QM Mast Arm (PRV & PRV-P)**




**MA=QM Mast Arm (PRV-XL)**




**ADJA=Adjustable Arm Pole Mount (PRV & PRV-P)**




**ADJA=Adjustable Arm Pole Mount (PRV-XL)**




**ADJA-WM=Adjustable Arm Wall Mount (PRV & PRV-P)**




**ADJA-WM=Adjustable Arm Wall Mount (PRV-XL)**



**ADJS=Adjustable Slipfitter 3 (PRV & PRV-P)**




**ADJS=Adjustable Slipfitter 3 (PRV-XL)**




## Mounting Details


### SA=QM Pole Mount Arm (PRV-M)




### WM=QM Wall Mount Arm (PRV-M)




### MA=QM Mast Arm (PRV-M)




### FMA=Fixed Mast Arm (PRV-M)




### DM=Direct Pole Mount Arm (PRV-M)




### Versatile Mount System



### ADJS=Adjustable Slipfitter (PRV-M)








### SP2=Adjustable Slipfitter 2-3/8\" (PRV-M)



## Mounting Details

### Mounting Configurations and EPAs

						
Housing Size	Tilt Angle (Degrees)	Arm Mount Single	Arm Mount 2 @ 180°	Arm Mount 2 @ 90°	Arm Mount 3 @ 90°	Arm Mount 4 @ 90°
Prevail Petite	0°	0.54	1.08	0.84	1.38	1.38
	60°	1.68	1.85	2.42	3.15	3.30
Prevail	0°	0.92	1.35	1.42	1.63	1.63
	60°	2.20	2.40	3.05	3.88	4.07
	60° + Full Drop Visor	2.20	2.40	3.25	4.28	4.47
Prevail XL	0°	1.12	2.25	2.13	2.52	2.52
	60°	3.99	4.30	5.26	6.51	6.79
	60° + Full Drop Visor	3.99	4.30	5.59	7.17	7.49
Prevail Maxx	0°	1.28	2.56	1.7	2.69	2.69
	60°	5.09	5.52	6.34	7.49	7.81

**NOTE:** For 2 PRV's mounted at 90°, requires minimum 3" square or 4" round pole for fixture clearance. For 2 PRV-XL's mounted at 90°, requires minimum 4" square or round pole for fixture clearance. Customer is responsible for engineering analysis to confirm pole and fixture compatibility for applications.

## Optical Configurations

PRV-P-C10/C15/C20/C25  
(4,900/6,900/9,800/11,800  
Nominal Lumens)




PRV-C15  
(7,100 Nominal Lumens)




PRV-C25/C40/C60  
(13,100/17,100/20,000  
Nominal Lumens)




PRV-XL-C75/C100/C125  
(26,100/31,000/36,300 Nominal Lumens)




PRV-XL-C150/C175  
(41,100/48,600 Nominal Lumens)



PRV-M-PA6X  
(50,000/60,000/70,000/80,000 Nominal Lumens)



### Optical Distributions



## Product Specifications

### Optics

- Precision molded polycarbonate optics

### Electrical

- 40°C minimum operating temperature
- 40°C maximum operating temperature
- >.9 power factor
- <20% total harmonic distortion
- Class 1 electronic drivers have expected life of 100,000 hours with <1% failure rate
- 0-10V dimming driver is standard with leads external to the fixture
- Standard MOV surge protective device designed to withstand 10kV of transient line surge

### Physical Characteristics

- Single-piece die-cast aluminum housing
- Tethered die-cast aluminum door
- Five-stage super TGIC polyester powder coat paint, 2.5 mil nominal thickness
- Finish is compliant to 3,000 hour salt spray standard (per ASTM B117)
- Versatile, patented, standard mount arm accommodates multiple drill patterns ranging from 1-1/2" to 4-7/8" (Type M drilling recommended for new installations)
- A knock-out on the standard mounting arm enables round pole mounting
- Adjustable pole and wall mount arms adjust in 5° increments from 0° to 60°; Downward facing orientation only (Type N drilling required for ADJA mount)
- Adjustable slipfitter arm adjusts in 5° increments from -5° to 85°; Downward facing orientation only

### Controls

- Luminaire available with the field adjustable dimming controller (FADC) to manually adjust wattage and reduce the total lumen output and light levels; Comes pre-set to the highest position at the lumen output selected

### Compliance

- DarkSky approved for 3000K CCT and warmer, with mounting options less than 10° of tilt.
- DLC and DLC Premium listed – visit [designlights.org](http://designlights.org) to confirm listed variations
- Prevail and Prevail Petite: 3G vibration rated
- Prevail XL Mast Arm: 3G vibration rated
- Prevail XL Standard Arm: 1.5G vibration rated
- Adjustable Arms: 1.5G vibration rated
- BAA domestic preference option meets BAA requirements. See [DOMESTIC.PREFERENCES](http://DOMESTIC.PREFERENCES) website or consult the CLS Domestic Preferences team for more information
- FHWA and FTA agencies are utilizing their BAA rules for BABA compliance. Cooper's products with a BAA designation are manufactured in the US and utilize a BAA COTS exemption rule for compliance. To verify a configured product with specific accessories and options meet BABA Domestic Preference Requirements; submit this catalog number to Cooper Lighting Quotation team for validation by our Engineering and Manufacturing teams. Please refer to the [DOMESTIC.PREFERENCES](http://DOMESTIC.PREFERENCES) website or consult the CLS Domestic Preferences team for more information. Components shipped separately may be separately analyzed under domestic preference requirements.

### Typical Applications

- Parking lots
- Walkways
- Roadways
- Building Areas

### Shipping Data

- Prevail Petite: 18 lbs. (7.94 kgs.)
- Prevail: 20 lbs. (9.09 kgs.)
- Prevail XL: 45 lbs. (20.41 kgs.)
- Prevail Maxx: 49 lbs. (22.23 kgs.)

### Warranty

- Five year limited warranty, consult website for details. [www.cooperlighting.com/legal](http://www.cooperlighting.com/legal)

## Energy and Performance Data



View PRV-P IES files



View PRV IES files



View PRV-XL IES files

## Power and Lumens

Product Family		Prevail Petite				Prevail				Prevail XL					Prevail Maxx			
Light Engine		C10	C15	C20	C25	C15	C25	C40	C60	C75	C100	C125	C150	C175	C200	C225	C250	C275
Power (Watts)		35	49	73	94	52	96	131	153	176	217	264	285	346	346	418	487	588
Input Current @ 120V (A)		0.29	0.41	0.61	0.79	0.43	0.80	1.09	1.32	1.50	1.84	2.21	2.38	2.92	2.89	3.49	4.06	4.90
Input Current @ 277V (A)		0.13	0.18	0.27	0.35	0.19	0.35	0.48	0.57	0.66	0.82	0.97	1.04	1.25	1.26	1.51	1.72	2.06
Input Current @ 347V (A)		0.11	0.16	0.23	0.29	0.17	0.30	0.41	0.48	0.54	0.66	0.79	0.84	1.02	1.00	1.21	1.40	1.70
Input Current @ 480V (A)		0.08	0.12	0.17	0.22	0.12	0.22	0.30	0.35	0.40	0.48	0.57	0.62	0.74	0.73	0.88	1.00	1.21
Distribution <sup>1</sup>																		
Type II	4000K Lumens	4,775	6,717	9,542	11,521	7,123	13,205	17,172	20,083	26,263	31,231	36,503	41,349	48,876	50,349	59,444	68,447	79,322
	BUG Rating	B1-U0-G1	B1-U0-G1	B2-U0-G2	B2-U0-G2	B2-U0-G2	B2-U0-G2	B3-U0-G3	B3-U0-G3	B3-U0-G3	B3-U0-G4	B4-U0-G4	B4-U0-G4	B4-U0-G5	B4-U0-G5	B4-U0-G5	B4-U0-G5	B5-U0-G5
	Lumens per Watt	138	137	131	122	137	138	131	131	149	144	138	145	141	146	142	141	135
	3000K Lumens <sup>1</sup>	4,869	6,595	9,369	11,312	6,994	12,965	16,860	19,718	25,786	30,664	35,840	40,598	47,989	49,437	58,368	67,208	77,886
Type III	4000K Lumens	4,782	6,727	9,556	11,538	7,111	13,183	17,144	20,050	26,120	31,061	36,304	41,124	48,610	50,162	59,223	68,193	79,027
	BUG Rating	B1-U0-G2	B1-U0-G2	B2-U0-G3	B2-U0-G3	B1-U0-G2	B2-U0-G3	B3-U0-G4	B3-U0-G4	B3-U0-G5	B3-U0-G5	B3-U0-G5	B4-U0-G5	B4-U0-G5	B4-U0-G5	B4-U0-G5	B5-U0-G5	B5-U0-G5
	Lumens per Watt	138	137	131	123	137	137	131	131	148	143	138	144	140	145	142	140	135
	3000K Lumens <sup>1</sup>	4,695	6,605	9,383	11,329	6,982	12,944	16,832	19,686	25,646	30,497	35,645	40,377	47,727	49,254	58,151	66,958	77,596
Type IV	4000K Lumens	4,880	6,865	9,752	11,774	7,088	13,140	17,087	19,984	26,098	31,035	36,274	41,089	48,569	50,575	59,711	68,754	79,678
	BUG Rating	B1-U0-G2	B1-U0-G2	B2-U0-G3	B2-U0-G3	B1-U0-G3	B2-U0-G4	B2-U0-G4	B3-U0-G5	B3-U0-G5	B3-U0-G5	B3-U0-G5	B3-U0-G5	B4-U0-G5	B4-U0-G5	B4-U0-G5	B4-U0-G5	B5-U0-G5
	Lumens per Watt	141	140	134	125	136	137	130	131	148	143	137	144	140	146	143	141	136
	3000K Lumens <sup>1</sup>	4,792	6,740	9,575	11,561	6,959	12,901	16,777	19,621	25,624	30,471	35,615	40,343	47,687	49,659	58,630	67,510	78,235
Type V	4000K Lumens	5,067	7,128	10,126	12,226	7,576	14,045	18,264	21,360	28,129	33,450	39,097	44,287	52,349	53,531	63,201	72,773	84,335
	BUG Rating	B3-U0-G2	B3-U0-G2	B4-U0-G3	B4-U0-G3	B3-U0-G3	B4-U0-G3	B4-U0-G4	B5-U0-G4	B5-U0-G5	B5-U0-G5	B5-U0-G5	B5-U0-G5	B5-U0-G5	B5-U0-G5	B5-U0-G5	B5-U0-G5	B5-U0-G5
	Lumens per Watt	146	145	139	130	146	146	139	140	160	154	148	155	151	155	151	150	144
	3000K Lumens <sup>1</sup>	4,975	6,999	9,942	12,004	7,438	13,790	17,932	20,972	27,618	32,843	38,387	43,483	51,398	52,562	62,057	71,455	82,808

## NOTES:

1. For 3000K, 5000K or HSS data, refer to published IES files.

### Lumen Maintenance

Configuration	TM-21 Lumen Maintenance (50,000 Hours)	Theoretical L70 (Hours)
Prevail and Prevail Petite at 25°C	91.30%	> 194,000
Prevail and Prevail Petite at 40°C	87.59%	> 134,000
Prevail XL at 25°C	91.40%	> 204,000
Prevail XL at 40°C	89.41%	> 158,000
Prevail Maxx at 25°C	91.40%	> 204,000
Prevail Maxx at 40°C	89.41%	> 158,000

### Lumen Multiplier

Ambient Temperature	Lumen Multiplier
10°C	1.02
15°C	1.01
25°C	1.00
40°C	0.99

### FADC Settings

FADC Position	Lumen Multiplier
1	25%
2	46%
3	55%
4	62%
5	72%
6	77%
7	82%
8	85%
9	90%
10	100%

Note: +/-5% typical value

### Sensor Color Reference Table (SPBx)




Housing Finish	Sensor Color
AP=Grey	Grey
BZ=Bronze	Bronze
BK=Black	Black
DP=Dark Platinum	Grey
GM=Graphite Metallic	Black
WH=White	White

## Control Options

**0-10V** This fixture provides 0-10V dimming wire leads for use with a lighting control panel or other control method.

**Photocontrol** (PR and PR7) Photocontrol receptacles provide a flexible solution to enable "dusk-to-dawn" lighting by sensing light levels. Advanced control systems compatible with NEMA 7-PIN standards can be utilized with the PR7 receptacles.

**Dimming Occupancy Sensor** (SPB, MS/DIM-LXX) These sensors are factory installed in the luminaire housing. When the SPB or MS/DIM sensor options are selected, the luminaire will dim down after five minutes of no activity detected. When activity is detected, the luminaire returns to full light output. These occupancy sensors include an integral photocell for "dusk-to-dawn" control or "daylight harvesting." Factory default is enabled for the MS sensors and disabled for the SPB. SPB motion sensors require the Sensor Configuration mobile application by Wattstopper to change factory default dimming level, time delay, sensitivity and other parameters. Available for iOS and Android devices. The SPB sensor is factory preset to dim down to approximately 10% power with a time delay of five minutes.



**WaveLinx Wireless Control and Monitoring System** Available in 7-PIN or 4-PIN configurations, the WaveLinx Outdoor control platform operates on a wireless mesh network based on IEEE 802.15.4 standards enabling wireless control of outdoor lighting. At least one Wireless Area Controller (WAC) is required for full functionality and remote communication (including adjustment of any factory pre-sets).

**WaveLinx Outdoor Control Module (WOLC-7P-10A)** A photocontrol that enables astronomical or time-based schedules to provide ON, OFF and dimming control of fixtures utilizing a 7-PIN receptacle. The out-of-box functionality is ON at dusk and OFF at dawn.

**WaveLinx Wireless Sensor (WPS2 and WPS4)** These outdoor sensors offer passive infrared (PIR) occupancy sensing and a photocell for closed-loop daylight sensing. These sensors are factory preset to dim down to approximately 50 percent power after 15 minutes of no activity detected, and the photocell for "dusk-to-dawn" control is default enabled. A variety of sensor lenses are available to optimize the coverage pattern for mounting heights from 7'-40'.

