

Quick Ship Program



Corelite - p. 2-4

Corelite



Neo-Ray - p.5-12

Neo-Ray



Shaper p. 12

Shaper

Corelite, Neo-Ray & Shaper Architectural Lighting




Stay ahead of demanding project schedules

The Quick Ship program focuses on the most popular and recently introduced LED luminaires that cover a wide array of architectural lighting applications.

The 10-day lead time on select products caters to fast moving construction projects and ensures that schedules are met and that projects are successful.




- ✓ Customizable Corelite, Neo-Ray & Shaper architectural products
- ✓ Suspended and recessed slot fixtures available up to 1,000 feet
For Quick Ship Orders over 1000 feet:
 - First 1000 feet will ship in 10 Days
 - Next 1000 feet will ship within 20 Days
- ✓ Options include: sensors and battery packs



Hugo - HGL Direct LED Linear Suspended Series

Corelite

- Architectural styling in a small scale profile
- Durable extruded aluminum housing with powder coat paint finish
- Frosted flush lens
- 750 to 2,000 delivered lumens per foot
- Up to 145 Lumens per Watt
- Aircraft cable suspended
- Rigid joining features for straight long runs
- Available in 4', 8', 12' and Continuous runs



Sample Number: QS-HGL-S-FR-30L835-1D-UNV-STD-ILB12-W-AC48-UM-4

Series	Size	Shielding/Optics	Lumen Package Nominal per 4' section	CRI / Color Temperature	Number of Circuits ¹	Additional Circu- iting	Input Voltage
QS-HGL=HUGO Linear LED, Quick Ship	S=Small	FR=Frosted Lens	30L=3,000 Lms (750 lms/ft) 40L=4,000 Lms (1,000 lms/ft) 50L=5,000 Lms (1,250 lms/ft) 60L=6,000 Lms (1,500 lms/ft) 80L=8,000 Lms (2,000 lms/ft)	835=3500K, 80+ CRI 840=4000K, 80+ CRI	1=1 Circuit	D=None (Default Dimming)	UNV=Universal (120V-277V)
Driver/Dimming Options	Integral Emergency ²	Finish	Suspension Length ³	Ceiling Type	Run Length ⁴		
STD=Standard 0-10V (1%-100%)	ILB12=12-watt battery pack, 120V-277V, Iota ILB-SL-CP12	W=White	Adj. Cable AC48=48" AC120=120"	UM=Universal Ceiling	4=4 ft. 8=8 ft. 12=12 ft. XX=Specify Row Length		

NOTES: 1. Refers to wiring in cross section. 2. 30°C max ambient temperature rating when integral battery selected. 3. UM ceiling type accommodates 1" Grid, 9/16" Grid, 4" Octagonal J-Box, and Structure ceiling types. Refer to ceiling interface installation instructions for more details. White mounting hardware standard. 4. Standard row configurations over 12' consist of 8' and 12' luminaires.



Jaylum - J2 Direct/Indirect Suspended Series

Corelite

- J2 series provides 25% Up / 75% down distribution using a single row of LEDs
- Architectural design and quality
- Wide array of distribution options with J2 and J3 series
- Multiple lumen packages (Up to 133 lumen per watt)
- Individual or continuous mounting
- Integral emergency battery packs available



Sample Number: QS-J2-WL-20L835-1D-UNV-STD-ILB12-W-AC48-T1-4

Series	Shielding ¹	Lumen Package Nominal per 4' section	CRI/Color Temperature		Number of Circuits ²	Additional Circuiting	Input Voltage
QS-J2 =Jaylum Suspended Direct/Indirect Quick Ship	WL =Frosted Lens (25% Up / 75% Dn)	20L =2,000 Lms (500 lms/ft) 30L =3,000 Lms (750 lms/ft) 40L =4,000 Lms (1,000 lms/ft) 50L =5,000 Lms (1,250 lms/ft)	835 =LED 3500K, 80+ CRI 840 =LED 4000K, 80+ CRI		1 =Single Circuit	D =None (Default Dimming)	UNV =Universal (120V-277V)
Driver/Dimming Options ³	Integral Emergency		Finish	Suspension Length ⁴	Ceiling Type		Run Length ⁵
STD =Standard 0-10V (1%-100%)	ILB12 =12-watt, 120V-277V Iota ILB-SL-CP12		W =White	<u>Adj. Cable</u> AC48 =48" AC120 =120"	T1 =1" T-Bar T9 =9/16" T-Bar TS =Slotted T-Bar ST =Structure JB =4" Octagonal J-Box		4 =4 ft 8 =8 ft XX =Specify Row Length

NOTES: 1. Additional distributions are available. See Jaylum J3 series. 2. Refers to wiring in cross section. 3. One driver per 4' section unless otherwise noted. 4. White mounting hardware standard. 5. Standard row configurations over 8' consist of 4' and 8' luminaires.



Jaylum - J3 Direct/Indirect Suspended Series

Corelite

- J3 series offers a wide optical distribution with up to 80% uplight
- Architectural design and quality
- Wide array of distribution options with J2 and J3 series
- Multiple lumen packages (Up to 157 lumen per watt)
- Individual or continuous mounting
- Integral emergency battery packs available



Sample Number: QS-J3-UL-20L835-1D-UNV-STD-ILB12-W-AC48-T1-4

Series	Indirect Shielding ¹	Direct Shielding	Lumen Package Nominal per 4' section	CRI/ Color Temperature		Number of Circuits ²	Additional Circuiting
QS-J3 =Jaylum Suspended Indirect/Direct, Quick Ship	U =Open Top (80% Up / 20% Dn) C =Clear Top Cover (75% Up / 25% Dn) F =Frosted Top Cover (65% Up / 35% Dn)	L =Frosted Lens	20L =2,000 Lms (500 lms/ft) 30L =3,000 Lms (750 lms/ft) 40L =4,000 Lms (1,000 lms/ft) 50L =5,000 Lms (1,250 lms/ft) 60L =6,000 Lms (1,500 lms/ft) 80L =8,000 Lms (2,000 lms/ft)	835 =LED 3500K, 80+ CRI 840 =LED 4000K, 80+ CRI		1 =Single Circuit	D =None (Default Dimming)
Input Voltage	Driver/Dimming Options ³	Integral Emergency	Finish	Suspension Length ⁴	Ceiling Type	Run Length	
UNV =Universal (120V-277V)	STD =Standard 0-10V (1%-100%)	ILB12 =12-watt, 120V-277V Iota ILB-SL-CP12	W =White	<u>Adj. Cable</u> AC48 =48" AC120 =120"	T1 =1" T-Bar T9 =9/16" T-Bar TS =Slotted T-Bar ST =Structure JB =4" Octagonal J-Box	4 =4 ft 8 =8 ft XX =Specify Row Length	

NOTES: 1. More distributions are available. See Jaylum J2 series. 2. Refers to wiring in cross section. 3. One driver per 4' section unless otherwise noted. 4. White mounting hardware standard. Standard row configurations over 8' consist of 4' and 8' luminaires.

CL Recessed Slot Linear 2" Series

Corelite

- 2" linear aperture size
- 4 ft. and 8 ft. lengths for individual or continuous runs in 4 ft. increments
- Frosted flush and asymmetric flush lens options
- High performance efficacy up to 122 lumens per watt
- Fits a variety of different architectural ceiling types
- Integrated wireless sensor control available



Sample Number: QS-CL2DR-F-30D835-1B3-UNV-STD-WAA-CP-W-T1-4

Light Distribution	Shielding Down ¹	Lumen Package Down ²	CCT & Min CRI	Circuiting ³	Emergency ⁴	Voltage
QS-CL2DR =Corelite CL Series 2" Aperture Direct Recessed Quick Ship	F =Frosted Flush Diffuser A =Asymmetric Flush Optic	30D =300 lumens/ft 50D =500 lumens/ft 70D =700 lumens/ft 90D =900 lumens/ft 100D =1000 lumens/ft	835 =3500K, 80+ CRI 840 =4000K, 80+ CRI	1 =Single Circuit S =Secondary Circuit	E =Emergency Circuit B3 =Iota 5-watt 120V-277V Integral EM Battery EPC =EPC UL924 Device	UNV =Universal (120-277V)
Integral LED Driver	Integrated Sensor ⁵	Options ⁶	Finish	Ceiling Type	Length ⁷	
STD =Standard 0-10V (1%-100%)	WAA =WaveLinx Wireless Integral Sensor	CP =Chicago Plenum	W =White	T1 =15/16" T-Grid, 9/16" T-Grid T2 =9/16" Slot T-Grid, 9/16" Tegular T-Grid FG =Flanged (Gypsum Board)	4 =4' Individual 8 =8' Individual XX =4' Incremental Run (e.g. 40=40')	

NOTES: 1. All lensing options are snap-in lenses. 2. Nominal lumen output. 3. Secondary circuit similar to A/B switching. Secondary circuit not available with sensor options. 4. Fixture Non-IC-Rated for internal battery and lumen output ≥1000 Lms/ft. External battery standard with Chicago plenum. 5. Sensor options must be used with 'STD' driver. Integral sensor not available with asymmetric lens option. 6. Meets CEC requirements. 7. Standard row configurations over 8' consist of 4' and 8' luminaires.



CL Recessed Slot Linear 4" Series

Corelite

- 4" linear aperture size
- 4 ft. and 8 ft. lengths for individual or continuous runs
- Highly efficient LED optical systems
- High performance efficacy up to 122 lumens per watt
- Fits a variety of different architectural ceiling types
- Integrated wireless sensor control available



Sample Number: QS-CL4DR-F-40D835-1B1-UNV-STD-WAA-CP-W-T1-4

Light Distribution	Shielding Down ¹	Lumen Package Down ²	CCT & Min CRI	Circuiting ³	Emergency ⁴	Voltage
QS-CL4DR =Corelite CL Series 4" Aperture Direct Recessed Quick Ship	F =Frosted Flush Diffuser A =Asymmetric Flush Optic	40D =400 lumens/ft 60D =600 lumens/ft 80D =800 lumens/ft 100D =1000 lumens/ft 120D =1200 lumens/ft	835 =3500K, 80+ CRI 840 =4000K, 80+ CRI	1 =Single Circuit S =Secondary Circuit	E =Emergency Circuit B1 =10-watt 120V-277V Integral EM Battery EPC =EPC UL924 Device	UNV =Universal (120-277V)
Integral LED Driver	Integrated Sensor ⁵	Options ⁶	Finish	Ceiling Type	Length ⁷	
STD =Standard 0-10V (1%-100%)	WAA =WaveLinx Wireless Integral Sensor	CP =Chicago Plenum	W =White	T1 =15/16" T-Grid, 9/16" T-Grid T2 =9/16" Slot T-Grid, 9/16" Tegular T-Grid FG =Flanged (Gypsum Board)	4 =4' Individual 8 =8' Individual XX =4' Incremental Run (e.g. 40=40')	

NOTES: 1. All lensing options are snap-in lenses. 2. Nominal lumen output. 3. Secondary circuit similar to A/B switching. Secondary circuit not available with sensor options. 4. Fixture Non-IC-Rated for internal battery and lumen output ≥1000 Lms/ft. External battery standard with Chicago plenum. 5. Sensor options must be used with 'STD' driver. Integral sensor not available with asymmetric lens option. 6. Meets CEC requirements. 7. Standard row configurations over 8' consist of 4' and 8' luminaires.

Define Gen 2 - 2" Recessed Linear Slot

Neo-Ray

- Specifiable to the nearest 4 ft. in length
- Satin Lens, Asymmetric Lens and Drop Lens available
- Multiple lumen packages
- Precision extruded trims fit a variety of different architectural ceiling types
- Industry leading performance and efficacy
- Contractor friendly installation with integral light leak blocking feature



Sample Number: QS-S122DR-S290D830-ETG4F0-1B3-UDD-F-CP-W-WAA



Light Distribution	Light Engine	Lumen Package Down ¹	CCT & Min CRI	Ceiling Type	Length	Circuiting ²
QS-S122DR =Define 2 Direct Recessed Quick Ship	S =Standard	290D =290 Lms/ft 485D =485 Lms/ft 675D =675 Lms/ft 865D =865 Lms/ft 1005D =1005 Lms/ft	830 =3000K, 80CRI 835 =3500K, 80CRI 840 =4000K, 80CRI	ETG =15/16" T-Grid FTG =9/16" T-Grid STG =9/16" Slot T-Grid FTT =9/16" Tegular T-Grid ITG =9/16" Interlude T-Grid GYP =Gypsum board	4FO =4' Individual 8FO =8' Individual _FO =4' Incremental Run (e.g. 40FO=40' 0")	1 =Single Circuit S =Secondary Circuit
Emergency ³	Voltage ⁶	Integral LED Driver ⁴	Shielding Down ⁵	Options	Color	Integrated Sensor ⁶
E =Emergency circuit B3 =Iota 5W UNV battery T =Iota UL924 ETR Emergency Bypass Relay	U =UNV 120-277V	DD =0-10 Volt Dimming, 1%	F =Satin Flush Diffuser A =Asym Flush Optic D =Satin Drop Diffuser	CP =Chicago Plenum	W =Matte White	WAA =WaveLinx Integral

NOTES: 1. 3500K/80CRI/DR housing/F Lens. 2. Secondary circuit similar to A/B switching. 3. Internal battery standard for fixtures ≥ 4ft and lumen output ≤865Lms/ft. Fixture Non-IC-Rated for internal battery and lumen output ≥ 1005 Lms/ft. External battery standard with Chicago plenum. 4. For non-dimming applications, the driver will default to full brightness if no connection is made to the capped dimming wires in the field. 5. All lensing options are snap-in lenses. 6. Integral sensor not available with drop or asymmetric configurations.

Define Gen 2 - 3" Recessed Linear Slot

Neo-Ray

- Specifiable to the nearest 4 ft. in length
- Satin Lens, Asymmetric Lens and Drop Lens available
- Multiple lumen packages
- Precision extruded trims fit a variety of different architectural ceiling types
- Industry leading performance and efficacy
- Contractor friendly installation with integral light leak blocking feature



Sample Number: QS-S123DR-S1000D840-ETG4F0-1B1-UDD-F-CP-W-WAA



Light Distribution ¹	Light Engine	Lumen Package Down ¹	CCT & Min CRI	Ceiling Type	Length	Circuiting ²
QS-S123DR =Define 3 Direct Recessed Quick Ship	S =Standard	340D =340 Lms/ft 560D =560 Lms/ft 775D =775 Lms/ft 1000D =1000 Lms/ft 1165D =1165 Lms/ft	830 =3000K, 80CRI 835 =3500K, 80CRI 840 =4000K, 80CRI	ETG =15/16" T-Grid FTG =9/16" T-Grid STG =9/16" Slot T-Grid FTT =9/16" Tegular T-Grid ITG =9/16" Interlude T-Grid GYP =Gypsum board	4FO =4' Individual 8FO =8' Individual _FO =4' Incremental Run (e.g. 40FO=40' 0")	1 =Single Circuit S =Secondary Circuit
Emergency ³	Voltage	Integral LED Driver ⁴	Shielding Down ⁵	Options	Color	Integrated Sensor ⁶
E =Emergency circuit B1 =Surelite 7W UNV battery B2 =Surelite 14W UNV battery T =Iota UL924 ETR Emergency Bypass Relay	U =UNV 120-277V	DD =0-10 Volt Dimming, 1%	F =Satin Flush Diffuser A =Asym Flush Optic D =Satin Drop Diffuser	CP =Chicago Plenum	W =Matte White	WAA =WaveLinx Integral

NOTES: 1. 3500K/80CRI/DR housing/F Lens. 2. Secondary circuit similar to A/B switching. 3. Internal battery standard for fixtures ≥ 4ft and lumen output ≤1000Lms/ft. Fixture Non-IC-Rated for internal battery and lumen output ≥ 1165 Lms/ft. External battery standard with Chicago plenum. 4. For non-dimming applications, the driver will default to full brightness if no connection is made to the capped dimming wires in the field. 5. All lensing options are snap-in lenses. 6. Integral sensor not available with drop or asymmetric configurations.



Define Gen 2 - 4" Recessed Linear Slot

Neo-Ray

- Specifiable to the nearest 4 ft. in length
- Satin Lens, Asymmetric Lens and Drop Lens available
- Multiple lumen packages
- Precision extruded trims fit a variety of different architectural ceiling types
- Industry leading performance and efficacy
- Contractor friendly installation with integral light leak blocking feature



Sample Number: QS-S124DR-S795D840-ETG4F0-1B1-UDD-F-CP-W-WAA

Light Distribution	Light Engine	Lumen Package Down ¹	CCT & Min CRI	Ceiling Type	Length	Circuiting ²
QS-S124DR =Define 4 Direct Recessed Quick Ship	S =Standard	350D =350 Lms/ft 575D =575 Lms/ft 795D =795 Lms/ft 1020D =1020 Lms/ft 1195D =1195 Lms/ft	830 =3000K, 80CRI 835 =3500K, 80CRI 840 =4000K, 80CRI	ETG =15/16" T-Grid FTG =9/16" T-Grid STG =9/16" Slot T-Grid FTT =9/16" Tegular T-Grid ITG =9/16" Interlude T-Grid GYP =Gypsum board	4FO =4' Individual 8FO =8' Individual _FO =4' Incremental Run (e.g. 40FO=40' 0")	1 =Single Circuit S =Secondary Circuit
Emergency ³	Voltage	Integral LED Driver ⁴	Shielding Down ⁵	Options	Color	Integrated Sensor ⁶
E =Emergency circuit B1 =Surelite 7W UNV battery B2 =Surelite 14W UNV battery T =Iota UL924 ETR Emergency Bypass Relay	U =UNV 120-277V	DD =0-10 Volt Dimming, 1%	F =Satin Flush Diffuser A =Asym Flush Optic D =Satin Drop Diffuser	CP =Chicago Plenum	W =Matte White	WAA =WaveLinX Integral

NOTES: 1. 3500K/80CRI/DR housing/F Lens. 2. Secondary circuit similar to A/B switching. 3. Internal battery standard for fixtures ≥ 4ft and lumen output ≤1020Lms/ft. Fixture Non-IC-Rated for internal battery and lumen output ≥ 1195 Lms/ft. External battery standard with Chicago plenum. 4. For non-dimming applications, the driver will default to full brightness if no connection is made to the capped dimming wires in the field. 5. All lensing options are snap-in lenses. 6. Integral sensor not available with drop or asymmetric configurations.

Define Gen 2 - 5" Recessed Linear Slot

Neo-Ray

- Specifiable to the nearest 4 ft. in length
- Satin Lens, Asymmetric Lens and Drop Lens available
- Multiple lumen packages
- Precision extruded trims fit a variety of different architectural ceiling types
- Industry leading performance and efficacy
- Contractor friendly installation with integral light leak blocking feature



Sample Number: QS-S125DR-S850D840-ETG4F0-1B1-UDD-F-CP-W-WAA

Light Distribution	Light Engine	Lumen Package Down ¹	CCT & Min CRI	Ceiling Type	Length	Circuiting ²
QS-S125DR =Define 5 Direct Recessed Quick Ship	S =Standard	375D =375 Lms/ft 610D =610 Lms/ft 850D =850 Lms/ft 1090D =1090 Lms/ft 1270D =1270 Lms/ft	830 =3000K, 80CRI 835 =3500K, 80CRI 840 =4000K, 80CRI	ETG =15/16" T-Grid FTG =9/16" T-Grid STG =9/16" Slot T-Grid FTT =9/16" Tegular T-Grid ITG =9/16" Interlude T-Grid GYP =Gypsum board	4FO =4' Individual 8FO =8' Individual _FO =4' Incremental Run (e.g. 40FO=40' 0")	1 =Single Circuit S =Secondary Circuit
Emergency ³	Voltage	Integral LED Driver ⁴	Shielding Down ⁵	Options	Color	Integrated Sensor ⁶
E =Emergency circuit B1 =Surelite 7W UNV battery B2 =Surelite 14W UNV battery T =Iota UL924 ETR Emergency Bypass Relay	U =UNV 120-277V	DD =0-10 Volt Dimming, 1%	F =Satin Flush Diffuser	CP =Chicago Plenum	W =Matte White	WAA =WaveLinX Integral

NOTES: 1. 3500K/80CRI/DR housing/F Lens. 2. Secondary circuit similar to A/B switching. 3. Internal battery standard for fixtures ≥ 4ft and lumen output ≤1090Lms/ft. Fixture Non-IC-Rated for internal battery and lumen output ≥ 1270 Lms/ft. External battery standard with Chicago plenum. 4. For non-dimming applications, the driver will default to full brightness if no connection is made to the capped dimming wires in the field. 5. All lensing options are snap-in lenses. 6. Integral sensor not available with drop or asymmetric configurations.



Define 2 - 2" LED Suspended Pendant

Neo-Ray

- Suspended Slot family in 2", 3", 4" and 5" housing sizes
- Specifiable to the nearest foot
- Satin, Asymmetric and Drop Direct Lensing available
- Independently specifiable Direct / Indirect lumen packages
- 0-10V dimming standard; DALI dimming available
- 2700K, 3000K, 3500K, 4000K, and 5000K correlated color temperatures available



Sample Number: S122DIP-C675D330U835-C4JB4F0-1T-UDD-F1-W-WAA

Series	Light Engine	Lumen Package Down (Lms/ft)	Lumen Package Up (Lms/ft)	CRI	LED CCT	Suspension Type
QS-S122DIP= Define 2 Direct/ Indirect Pendant Quick Ship	C=Core	290D =290 Lms/ft (2.9W/ft) 485D =485 Lms/ft (4.8W/ft) 675D =675 Lms/ft (6.7W/ft) 865D =865 Lms/ft (8.8W/ft) 1005D =1005 Lms/ft (10.6W)	330U =330 Lms/ft (2.2W/ft) 530U =530 Lms/ft (3.6W/ft) 725U =725 Lms/ft (5.0W/ft) 925U =925 Lms/ft (6.6W/ft) 1080U =1080 Lms/ft (7.9W)	8 =80	30 =3000K 35 =3500K 40 =4000K	C4 =4ft Aircraft Cable C10 =10ft Aircraft Cable C20 =20ft Aircraft Cable
Notes	Notes	Notes	Notes	Notes	Notes	Notes
RDIP regress of 1" will add an additional 1" to fixture depth.	See performance table for add'l details. Light engine must be consistent across run length. V option requires lumen package of 675 Lms/ft or greater and fixture length of 3 ft+.	3500K/80CRI/DIP/F Lens. Please refer to scaling data for other variables. For custom lumen output, please refer to additional information on page 3.	500K/80CRI/No Lens. Please refer to scaling data for other variables. For custom lumen output, please refer to additional information on page 3. 1080 Lms/ft not valid with DALI or Lutron Drivers. 330 Lms/ft available on fixture length 4ft+.	Additional lead-time and cost may apply for 927, 930, 935 and 940 configurations. 2765/3050 VividTune configurations require V light engine and W2A driver.		

Ceiling Type	Mounting HW Color	Luminaire Length (Ft)	Max section length	Circuiting	Additional Section Wiring
JB =Gypsum Board, Junction Box, Structure T1 =15/16" T-Grid (ETG) T9 =9/16" T-Grid (FTG) TS =9/16" Slot (STG), Tegal (FTT), Interlude (ITG)	(blank) =White B =Black	4F0 = 4' Nominal Length 8F0 =8' Nominal Length F0 =4' Incremental Run (e.g. 40F0=40' 0")	/8 =8ft	1 =Single Circuit 2 =Dual Circuit S =Secondary Circuit	E =Emergency Circuit B3 =Iota Slimline 5W, 120V-277V Integral (ILB-SL-CP5) T =UL924 EPC Emergency Bypass Relay
Notes	Notes	Notes	Notes	Notes	Notes
	White mounting hardware standard	Minimum fixture length is 3ft. Specify to nearest foot in length.	Individual fixtures configured as 12ft max by default. Continuous runs configured as 8ft max (12ft not available).	Dual circuit will provide separate Up/Down control. Secondary circuit similar to A/B switching. Price adder applies for "S" configuration.	Battery available on fixture ≥ 4ft in length. B3 and T options not compatible with 347V. Standard battery 4ft battery section located in the beginning of the fixture, but can be relocated using the linear product configurator.

Voltage	Driver Type	Shielding Down	Shielding Up	Finish	Integrated Sensor
U =Universal (120V-277V)	DD =Standard 0-10V Dimming (1%-100%)	F =Satin White Diffuser D =Satin Drop diffuser A =Asymmetric Diffuser	(blank) =No Lens or N/A 1 =Satin White Lay-in Diffuser	W =White S =Silver B =Black	WAA =WaveLinX Wireless
Notes	Notes	Notes	Notes	Notes	Notes
Native 347V only available with DD driver option.	DD driver is standard. For non-dimming applications, the driver will default to full brightness if no connection is made to the capped dimming wires in the field.	All lensing options are snap-in lenses. "L" option required RDIP series and will require additional lead-time, please consult factory for details.	No lens up standard, use satin white diffuser when dust cover desired of top of the fixture is viewable during normal use.	Contact factory for C and R options. W/S/B are standard.	DD driver must be selected. Please refer to page 5 for additional detail required to specify integrated sensors. Integral option not available with regressed or drop lensing. Battery not compatible with integrated sensor in 4ft DIP fixture.

Define 3 - 3" LED Suspended Pendant

Neo-Ray

- Suspended Slot family in 2", 3", 4" and 5" housing sizes
- Specifiable to the nearest foot
- Satin, Asymmetric and Drop Direct Lensing available
- Independently specifiable Direct / Indirect lumen packages
- 0-10V dimming standard; DALI dimming available
- 2700K, 3000K, 3500K, 4000K, and 5000K correlated color temperatures available



Sample Number: S123DIP-C675D330U835-C4JB4F0-1T-UDD-F1-W-WAA

Series	Light Engine	Lumen Package Down (Lms/ft)	Lumen Package Up (Lms/ft)	CRI	LED CCT	Suspension Type
QS-S123DIP =Define 3 Direct/Indirect Pendant Quick Ship	C =Core	340D =340 Lms/ft (2.9W/ft) 560D =560 Lms/ft (4.8W/ft) 775D =775 Lms/ft (6.7W/ft) 1000D =1000 Lms/ft (8.8W/ft) 1165D =1165 Lms/ft (10.6W)	365U =365 Lms/ft (2.2W/ft) 585U =585 Lms/ft (3.6W/ft) 805U =805 Lms/ft (5.0W/ft) 1025U =1025 Lms/ft (6.6W/ft) 1195U =1195 Lms/ft (7.9W)	8 =80	30 =3000K 35 =3500K 40 =4000K	C4 =4ft Aircraft Cable C10 =10ft Aircraft Cable C20 =20ft Aircraft Cable
Notes	Notes	Notes	Notes	Notes	Notes	Notes
RDIP regress of 1" will add an additional 1" to fixture depth.	See performance table for add'l details. Light engine must be consistent across run length. V option requires lumen package of 775 lms/ft or greater and fixture length of 3 ft+.	3500K/80CRI/DIP/F Lens. Please refer to scaling data for other variables. For custom lumen output, please refer to additional information on page 3. 1165 Lms/ft not valid with DALI or Lutron Drivers. 340 Lms/ft available on fixture length 4ft+.	3500K/80CRI/No Lens. Please refer to scaling data for other variables. For custom lumen output, please refer to additional information on page 3	Additional lead-time and cost may apply for 927, 930, 935 and 940 configurations. 2765/3050 VividTune configurations require V light engine and W2A driver.		

Ceiling Type	Mounting HW Color	Luminaire Length (Ft)	Max section length	Circuiting	Additional Section Wiring
JB =Gypsum Board, Junction Box, Structure T1 =15/16" T-Grid (ETG) T9 =9/16" T-Grid (FTG) TS =9/16" Slot (STG), Tegal (FTT), Interlude (ITG)	(blank) =White B =Black	4F0 = 4' Nominal Length 8F0 =8' Nominal Length F0 =4' Incremental Run (e.g. 40F0=40' 0")	8 =8ft	1 =Single Circuit S =Secondary Circuit	E =Emergency Circuit B3 =Iota Slimline 5W, 120V-277V Integral (ILB-SL-CP5) T =UL924 EPC Emergency Bypass Relay
Notes	Notes	Notes	Notes	Notes	Notes
	White mounting hardware standard	Minimum fixture length is 3ft Specify to nearest foot in length.	Individual fixtures configured as 12ft max by default. Continuous runs configured as 8ft max (12ft not available).	Dual circuit will provide separate Up/Down control. Secondary circuit similar to A/B switching. Price adder applies for "S" configuration.	Battery available on fixture ≥ 4ft in length. B1-B3 and T options not compatible with 347V. Standard battery 4ft battery section located in the beginning of the fixture, but can be relocated using the linear product configurator.



Voltage	Driver Type	Shielding Down	Shielding Up	Finish	Integrated Sensor
U =Universal (120V-277V)	DD =Standard 0-10V Dimming (1%-100%)	F =Satin White Diffuser D =Satin Drop diffuser A =Asymmetric Diffuser	(blank) =No Lens or N/A 1 =Satin White Lay-in Diffuser	W =White S =Silver B =Black	WAA =WaveLinX Wireless
Notes	Notes	Notes	Notes	Notes	Notes
Native 347V only available with DD driver option.	DD driver is standard. For non-dimming applications, the driver will default to full brightness if no connection is made to the capped dimming wires in the field.	All lensing options are snap-in lenses.	No lens up standard, use satin white diffuser when dust cover desired of top of the fixture is viewable during normal use.	Contact factory for C and R options. W/S/B are standard.	DD driver must be selected. Please refer to page 5 for additional detail required to specify integrated sensors. Integral option not available with regressed or drop lensing. Battery not compatible with integrated sensor in 4ft DIP fixture.



Define 4 - 4" LED Suspended Pendant

Neo-Ray

- Suspended Slot family in 2", 3", 4" and 5" housing sizes
- Specifiable to the nearest foot
- Satin, Asymmetric and Drop Direct Lensing available
- Independently specifiable Direct / Indirect lumen packages
- 0-10V dimming standard; DALI dimming available
- 2700K, 3000K, 3500K, 4000K, and 5000K correlated color temperatures available



Sample Number: S124DIP-C795D365U835-C4JB4F0-1T-UDD-F1-W-WAA

Series	Light Engine	Lumen Package Down (Lms/ft)	Lumen Package Up (Lms/ft)	CRI	LED CCT	Suspension Type
QS-S124DIP = Define 4 Direct/ Indirect Pendant Quick Ship	C =Core	350D =350 Lms/ft (2.9W/ft) 575D =575 Lms/ft (4.8W/ft) 795D =795 Lms/ft (6.7W/ft) 1020D =1020 Lms/ft (8.8W/ft) 1195D =1195 Lms/ft (10.6W)	365U =365 Lms/ft (2.2W/ft) 590U =590 Lms/ft (3.6W/ft) 810U =810 Lms/ft (5.0W/ft) 1035U =1035 Lms/ft (6.6W/ft) 1205U =1205 Lms/ft (7.9W)	8 =80	30 =3000K 35 =3500K 40 =4000K	C4 =4ft Aircraft Cable C10 =10ft Aircraft Cable C20 =20ft Aircraft Cable
Notes	Notes	Notes	Notes	Notes	Notes	Notes
RDIP regress of 1" will add an additional 1" to fixture depth.	See performance table for add'l details. Light engine must be consistent across run length. V option requires lumen package of 795 lms/ft or greater and fixture length of 3 ft+.	3500K/80CRI/DIP/F Lens. Please refer to scaling data for other variables. For custom lumen output, please refer to additional information on page 3. 1195 Lms/ft not valid with DALI or Lutron Drivers. 350 Lms/ft available on fixture length 4ft+.	3500K/80CRI/No Lens. Please refer to scaling data for other variables.	Additional lead-time and cost may apply for 850, 927, 930, 935, 940 and 950 configurations. 2765/3050 VividTune configurations require V light engine and W2A driver.		

Ceiling Type	Mounting HW Color	Luminaire Length (Ft)	Max section length	Circuiting	Additional Section Wiring
JB =Gypsum Board, Junction Box, Structure T1 =15/16" T-Grid (ETG) T9 =9/16" T-Grid (FTG) TS =9/16" Slot (STG), Tegalur (FTT), Interlude (ITG)	(blank) = White B =Black	4F0 = 4' Nominal Length 8F0 =8' Nominal Length __F0 =4' Incremental Run (e.g. 40F0=40' 0")	/8 =8ft	1 =Single Circuit 2 =Dual Circuit S =Secondary Circuit	E =Emergency Circuit B1 =Surelite 7W 120-277V EM battery pack (EL7W) B2 =Surelite 14W 120-277V EM battery pack (EL14W) B3 =Iota Slimline 5W, 120V-277V Integral (ILB-SL-CP5) T =UL924 EPC Emergency Bypass Relay
Notes	Notes	Notes	Notes	Notes	Notes
	White mounting hardware standard	Minimum fixture length is 3ft. Specify to nearest foot in length.	Individual fixtures configured as 12ft max by default. Continuous runs configured as 8ft max (12ft not available).	Dual circuit will provide separate Up/Down control. Secondary circuit similar to A/B switching. Price adder applies for "S" configuration.	Battery available on fixture ≥ 4ft in length. B1-B3 and T options not compatible with 347V. Standard battery 4ft battery section located in the beginning of the fixture, but can be relocated using the linear product configurator.

Voltage	Driver Type	Shielding Down	Shielding Up	Finish	Integrated Sensor
U =Universal (120V-277V)	DD =Standard 0-10V Dimming (1%-100%)	F =Satin White Diffuser D =Satin Drop diffuser A =Asymmetric Diffuser	(blank) =No Lens or N/A 1 =Satin White Lay-in Diffuser	W =White S =Silver B =Black	WAA =WaveLinx Wireless
Notes	Notes	Notes	Notes	Notes	Notes
347V only available with DD driver options.	DD driver is standard. For non-dimming applications, the driver will default to full brightness if no connection is made to the capped dimming wires in the field.	All lensing options are snap-in lenses. "L" option required RDIP series and will require additional lead-time, please consult factory for details.	No lens up standard, use satin white diffuser when dust cover desired of top of the fixture is viewable during normal use.	Contact factory for C and R options. W/S/B are standard.	DD driver must be selected. Integral option not available with regressed or drop lensing. Battery not compatible with integrated sensor in 4ft DIP fixture.

Define 2 - 2" LED Suspended Pendant Direct

Neo-Ray

- Suspended Slot family in 2", 3", 4" and 5" housing sizes
- Specifiable to the nearest foot
- Satin, Asymmetric and Drop Direct Lensing available
- Independently specifiable Direct / Indirect lumen packages
- 0-10V dimming standard; DALI dimming available
- 2700K, 3000K, 3500K, 4000K, and 5000K correlated color temperatures available



Sample Number: S122DP-C675D835-C4JB4F0-1T-UDD-F-W-WAA

Series	Light Engine	Lumen Package Down (Lms/ft)	CRI	LED CCT	Suspension Type	Ceiling Type
QS-S122DP = Define 2 Direct Pendant Quick Ship	C =Core	290D =290 Lms/ft (2.9W/ft) 485D =485 Lms/ft (4.8W/ft) 675D =675 Lms/ft (6.7W/ft) 865D =865 Lms/ft (8.8W/ft) 1005D =1005 Lms/ft (10.6W)	8 =80	30 =3000K 35 =3500K 40 =4000K	C4 =4ft Aircraft Cable C10 =10ft Aircraft Cable C20 =20ft Aircraft Cable	JB =Gypsum Board, Junction Box, Structure T1 =15/16" T-Grid (ETG) T9 =9/16" T-Grid (FTG) TS =9/16" Slot (STG), Tegular (FTT), Interlude (ITG)

Notes	Notes	Notes	Notes	Notes	Notes
RDP regress of 1" will add an additional 1" to fixture depth.	See performance table for add'l details. Light engine must be consistent across run length. V option requires lumen package of 675 lms/ft or greater.	3500K/80CRI/DIP/F Lens. Please refer to scaling data for other variables. For custom lumen output, please refer to additional information on page 3. 290 Lms/ft not available on 2ft fixture length.	Additional lead-time and cost may apply for 927, 930, 935 and 940 configurations. 2765/3050 VividTune configurations require V light engine and W2A driver.		

Mounting HW Color	Luminaire Length (Ft)	Max section length	Circuiting	Additional Section Wiring
(blank) =White B =Black	4F0 = 4' Nominal Length 8F0 =8' Nominal Length __F0 =4' Incremental Run (e.g. 40F0=40' 0")	/8 =8ft	1 =Single Circuit 2 =Dual Circuit S =Secondary Circuit	E =Emergency Circuit B3 =Iota Slimline 5W, 120V-277V Integral (ILB-SL-CP5) T =UL924 EPC Emergency Bypass Relay

Notes	Notes	Notes	Notes	Notes
White mounting hardware standard.	Minimum fixture length is 2ft. Specify to nearest foot in length.	Individual fixtures configured as 12ft max by default. Continuous runs configured as 8ft max (12ft not available).	Secondary circuit similar to A/B switching. Price adder applies for "S" configuration.	Battery available on fixture ≥ 4ft in length. B3 and T options not compatible with 347V. Standard battery 4ft battery section located in the beginning of the fixture, but can be relocated using the linear product configurator.


Voltage	Driver Type	Shielding Down	Finish	Integrated Sensor
U =Universal (120V-277V)	DD =Standard 0-10V Dimming (1%-100%)	F =Satin White Diffuser D =Satin Drop diffuser A =Asymmetric Diffuser	W =White S =Silver B =Black	WAA =WaveLinX Wireless
Notes	Notes	Notes	Notes	Notes
347V only available with DD driver option.	DD driver is standard. For non-dimming applications, the driver will default to full brightness if no connection is made to the capped dimming wires in the field.	All lensing options are snap-in lenses. "L" option required RDP series and will require additional lead-time, please consult factory for details.	Contact factory for C and R options. W/S/B are standard.	DD driver must be selected. Please refer to page 5 for additional detail required to specify integrated sensors. Integral option not available with regressed or drop lensing.



Define 3 - 3" LED Suspended Pendant Direct

Neo-Ray

- Suspended Slot family in 2", 3", 4" and 5" housing sizes
- Specifiable to the nearest foot
- Satin, Asymmetric and Drop Direct Lensing available
- Independently specifiable Direct / Indirect lumen packages
- 0-10V dimming standard; DALI dimming available
- 2700K, 3000K, 3500K, 4000K, and 5000K correlated color temperatures available



Sample Number: S123DP-C775D835-C4JB4F0-1T-UDD-F-W-WAA

Series	Light Engine	Lumen Package Down (Lms/ft)	CRI	LED CCT	Suspension Type	Ceiling Type
QS S123DP = Define 3 Direct Pendant Quick Ship	C =Core	340D =340 Lms/ft (2.9W/ft) 560D =560 Lms/ft (4.8W/ft) 775D =775 Lms/ft (6.7W/ft) 1000D =1000 Lms/ft (8.8W/ft) 1165D =1165 Lms/ft (10.6W)	8 =80	30 =3000K 35 =3500K 40 =4000K	C4 =4ft Aircraft Cable C10 =10ft Aircraft Cable C20 =20ft Aircraft Cable	JB =Gypsum Board, Junction Box, Structure T1 =15/16" T-Grid (ETG) T9 =9/16" T-Grid (FTG) TS =9/16" Slot (STG), Tegular (FTT), Interlude (ITG)
Notes	Notes	Notes	Notes	Notes	Notes	Notes
RDP regress of 1" will add an additional 1" to fixture depth.	See performance table for add'l details. Light engine must be consistent across run length. V option requires lumen package of 775 lms/ft or greater.	3500K/80CRI/DIP/F Lens. Please refer to scaling data for other variables. For custom lumen output, please refer to additional information on page 3. 340 Lms/ft not available on 2ft fixture length.	Additional lead-time and cost may apply for 927, 930, 935 and 940 configurations. 2765/3050 VividTune configurations require V light engine and W2A driver.			
Mounting HW Color	Luminaire Length (Ft)	Max section length	Circuiting	Additional Section Wiring		
(blank) =White B =Black	4F0 = 4' Nominal Length 8F0 =8' Nominal Length __F0 =4' Incremental Run (e.g. 40F0=40' 0")	/8 =8ft	1 =Single Circuit S =Secondary Circuit	E =Emergency Circuit B1 =Surelite 7W 120-277V EM battery pack (EL7W) B2 =Surelite 14W 120-277V EM battery pack (EL14W)		
Notes	Notes	Notes	Notes	Notes		
White mounting hardware standard.	Minimum fixture length is 2ft. Specify to nearest foot in length.	Individual fixtures configured as 12ft max by default. Continuous runs configured as 8ft max (12ft not available).	Secondary circuit similar to A/B switching. Price adder applies for "S" configuration.	Battery available on fixture ≥ 4ft in length. B1-B2 and T options not compatible with 347V. Standard battery 4ft battery section located in the beginning of the fixture, but can be relocated using the linear product configurator.		
Voltage	Driver Type	Shielding Down	Finish	Integrated Sensor		
U =Universal (120V-277V)	DD =Standard 0-10V Dimming (1%-100%)	F =Satin White Diffuser D =Satin Drop diffuser A =Asymmetric Diffuser	W =White S =Silver B =Black	WAA =WaveLinx Wireless		
Notes	Notes	Notes	Notes	Notes		
347V only available with DD driver option.	DD driver is standard. For non-dimming applications, the driver will default to full brightness if no connection is made to the capped dimming wires in the field.	All lensing options are snap-in lenses.	W/S/B are standard.	DD driver must be selected. Integral option not available with regressed or drop lensing.		



Define 4 - 4" LED Suspended Pendant Direct

Neo-Ray

- Suspended Slot family in 2", 3", 4" and 5" housing sizes
- Specifiable to the nearest foot
- Satin, Asymmetric and Drop Direct Lensing available
- Independently specifiable Direct / Indirect lumen packages
- 0-10V dimming standard; DALI dimming available
- 2700K, 3000K, 3500K, 4000K, and 5000K correlated color temperatures available



Sample Number: S124DP-C795D835-C4JB4F0-1T-UDD-F-W-WAA

Series	Light Engine	Lumen Package Down (Lms/ft)	CRI	LED CCT	Suspension Type	Ceiling Type
QS-S124DP = Define 4 Direct Pendant Quick Ship	C =Core	350D =350 Lms/ft (2.9W/ft) 575D =575 Lms/ft (4.8W/ft) 795D =795 Lms/ft (6.7W/ft) 1020D =1020 Lms/ft (8.8W/ft) 1195D =1195 Lms/ft (10.6W)	8 =80	30 =3000K 35 =3500K 40 =4000K	C4 =4ft Aircraft Cable C10 =10ft Aircraft Cable C20 =20ft Aircraft Cable	JB =Gypsum Board, Junction Box, Structure T1 =15/16" T-Grid (ETG) T9 =9/16" T-Grid (FTG) TS =9/16" Slot (STG), Tegalur (FTT), Interlude (ITG)
Notes	Notes	Notes	Notes	Notes	Notes	Notes
RDP regress of 1" will add an additional 1" to fixture depth.	See performance table for add'l details. Light engine must be consistent across run length. V option requires lumen package of 795 lms/ ft or greater.	3500K/80CRI/DIP/F Lens. Please refer to scaling data for other variables. For custom lumen output, please refer to additional information on page 3. 350 Lms/ft not available on 2ft fixture length.	Additional lead-time and cost may apply for 927, 930, 935 and 940 configurations. 2765/3050 VividTune configurations require V light engine and W2A driver.			
Mounting HW Color	Luminaire Length (Ft)	Max section length	Circuiting	Additional Section Wiring		
(blank)=White B =Black	4F0 = 4' Nominal Length 8F0 =8' Nominal Length ___F0 =4' Incremental Run (e.g. 40F0=40' 0")	/8=8ft	1 =Single Circuit S =Secondary Circuit	E =Emergency Circuit B1 =Surelite 7W 120-277V EM battery pack (EL7W) B2 =Surelite 14W 120-277V EM battery pack (EL14W) T =UL924 EPC Emergency Bypass Relay		
Notes	Notes	Notes	Notes	Notes		
White mounting hardware standard	Minimum fixture length is 2ft. Specify to nearest foot in length.	Individual fixtures configured as 12ft max by default. Continuous runs configured as 8ft max (12ft not available).	Secondary circuit similar to A/B switching. Price adder applies for "S" configuration.	Battery available on fixture ≥ 4ft in length. B1-B2 and T options not compatible with 347V. Standard battery 4ft battery section located in the beginning of the fixture, but can be relocated using the linear product configurator.		
Voltage	Driver Type	Shielding Down	Finish	Integrated Sensor		
U =Universal (120V-277V)	DD =Standard 0-10V Dimming (1%-100%)	F =Satin White Diffuser D =Satin Drop diffuser A =Asymmetric Diffuser	W =White S =Silver B =Black	WAA =WaveLinx Wireless		
Notes	Notes	Notes	Notes	Notes		
347V only available with DD driver option.	DD driver is standard. For non-dimming applications, the driver will default to full brightness if no connection is made to the capped dimming wires in the field.	All lensing options are snap-in lenses. "L" option required RDP series and will require additional lead-time, please consult factory for details.	Contact factory for C and R options. W/S/B are standard.	DD driver must be selected. Integral option not available with regressed or drop lensing.		

Shaper Sense™ Square Pendant Suspended

Shaper

- The Shaper Sense Square is a 1/2" edge lit floating square, that truly embodies the concept of minimalistic light and produces uniform light distribution. When turned off, is a window in the space, allowing natural light to pass through (85% transparent).
- Shaper Sense Square can be upgraded to award winning Shaper Sense Box and Trapezoid Acoustics products with addition of acoustic shade at later date.



Fixture Number Sample: ShSe-SQR-1-L40-80-UNV-CNPY-STD

Series	Shape/Family	Light Level / CCT / CRI (Lumens Wattage, Color Temp, CRI)	Voltage	Mounting	Dimming	Finish	Controls
QS= Shaper Sense Quick Ship	SQR= Square shaped light fixture	1-L30-90 =2579 lumens, 30W, 3000K, 90 CRI 1-L35-80 =3206 lumens, 30W, 3500K, 80 CRI 1-L40-80 =3148 lumens, 30W, 4000K, 80 CRI 2-L30-90 =3298 lumens, 39W, 3000K, 90 CRI 2-L35-80 =4104 lumens, 39W, 3500K, 80 CRI 2-L40-80 =4027 lumens, 39W, 4000K, 80 CRI	UNV =Universal Voltage (120-277)	CNPY =Canopy mount (works for surface, open structure, and gypsum ceilings)	STD =0-10V	White	WTA =Factory installed Wavelinx Sensor
Notes	Notes	Notes	Notes	Notes	Notes	Notes	Notes
		3000K – only in 90 CRI, 3500K only available in 80 CRI, 4000K only available in 80 CRI.					



Lighting Product Lines

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
Halo
Halo Commercial
Halo Outdoor
Invue
io
Iris
Lumark
Lumière
McGraw-Edison
Metalux
MWS
Neo-Ray
Portfolio
RSA
Shaper
Streetworks
Sure-Lites

Controls Product Lines

Fifth Light Technology
Greengate
iLight (International Only)
iLumin
Zero 88

Connected Lighting Systems

Distributed Low-Voltage Power
Halo Home
iLumin Plus
WaveLinx
Trellix

**Cooper Lighting Solutions**

1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2020 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
April 2020