

DESCRIPTION

The M Series combines a low profile, surface modular design with the latest in energy-efficient technology. The dihedral recessed top design allows for cooler fixture operation. Other features include a die-formed housing, surface or stem mounting (single or continuous row), full seam-welded corners and a broad selection of attractive door frames.

The versatile modular M Series can be the perfect solution when used in applications such as commercial office spaces, schools, hospitals, and retail merchandising.

SPECIFICATION FEATURES

Construction

Housing Die formed code gauge prime cold rolled steel. Smooth sides permit flush joint for continuous row mounting. Full seam welded corners. Dihedral recessed top design insures cooler ballast operation. Die formed captive lampholder bracket fully encloses wiring permitting easy lampholder replacement. Ballast covers easily removed without tools.

Electrical*

Ballasts are CBM/ETL Class "P" and are positively secured by mounting bolts. Pressure lock lampholders. UL/CUL listed. Suitable for damp locations.

Finish


Painted after fabrication. Electrostatically applied baked white polyester powder enamel finish. Multistage cleaning cycle, iron phosphate coating with rust inhibitor. Conveyorized application and baking timing accurately controlled at an elevated temperature.

Hinging/Latching

Positive cam action steel latches with baked white enamel finish. Safety lock T-hinges allow hinging and latching either side.

Frame/Shielding

Die formed, heavy gauge, flat steel door. Baked white enamel finish. Reinforced, mitered door frame corners. Door frame quadsealed to prevent light spillage. Light stabilized 100% virgin acrylic prismatic shielding. Standard #12 pattern. Optional shielding available.




2M
232
432

2' X 4' SURFACE
2 OR 4 LAMPS

Surface Modular

MOUNTING DATA




STEM MOUNTING METHODS

Consult Pre Sales Technical Support for Continuous Row Application


Fixture Application

4 Point Suspension




LAMP CONFIGURATIONS

2 LAMP




4 LAMP




DOOR FRAMES

2M



2MXF



2MSR



2MXR



2MXRD



ENERGY DATA

Input Watts:

EB Ballast & STD Lamps

232 (61)

432 (122)

Luminaire Efficacy Rating

LER = FL-71

Catalog Number: 2M-432A


Yearly Cost of 1000 lumens, 3000 hrs at .08 KWH = \$3.38

*Reference the lamp/ballast data in the Technical Section for specific lamp/ballast requirements.

LAMPS CONTAIN MERCURY. DISPOSE ACCORDING TO LOCAL, STATE OR FEDERAL LAWS

LINEAR DISCONNECT

Safe and convenient means of disconnecting power.



2M-432A125
Energy Saving Ballast

F32T8/35K Lamps
2900 Lumens

Spacing criterion:
(||) 1.3 x mounting height, (⊥) 1.4 x mounting height

Efficiency 77.2%

Test Report:
2M432A125.IES

LER = FL-71

Yearly Cost of 1000 lumens, 3000 hrs at .08 KWH = \$3.38

Coefficients of Utilization

rc	Effective floor cavity reflectance								20%															
	80%				70%				50%				30%				10%				0%			
rw	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																								
0	92	92	92	92	90	90	90	90	86	86	86	82	82	82	79	79	79	77	77	77	77	77	77	77
1	85	82	79	76	83	80	78	75	77	75	73	74	72	71	71	70	69	67	67	67	67	67	67	67
2	79	73	68	65	77	72	67	64	69	65	62	66	64	61	64	62	60	58	58	58	58	58	58	58
3	73	65	60	55	71	64	59	55	62	58	54	60	56	53	58	55	52	51	51	51	51	51	51	51
4	67	59	52	48	65	58	52	47	56	51	47	54	50	46	52	49	46	44	44	44	44	44	44	44
5	61	52	46	41	60	51	45	41	50	44	40	48	44	40	47	43	40	38	38	38	38	38	38	38
6	57	47	41	36	55	46	40	36	45	39	35	44	39	35	43	38	35	33	33	33	33	33	33	33
7	52	42	36	31	51	42	36	31	41	35	31	39	35	31	38	34	31	29	29	29	29	29	29	29
8	48	38	32	27	47	37	31	27	36	31	27	36	30	27	35	30	27	25	25	25	25	25	25	25
9	44	34	28	24	43	34	28	23	33	27	23	32	27	23	31	27	23	22	22	22	22	22	22	22
10	41	31	25	21	40	31	25	21	30	24	21	29	24	21	28	24	20	19	19	19	19	19	19	19

Zonal Lumen Summary

Zone	Lumens	%Lamp	%Fixture
0-30	2747	23.7	30.7
0-40	4554	39.3	50.8
0-60	7620	65.7	85.1
0-90	8958	77.2	100.0
0-180	8958	77.2	100.0

Typical VCP Percentages

Room Size (Ft.)	Height Along		Height Across	
	8.5'	10.0'	8.5'	10.0'
20 x 20	58	62	56	60
30 x 30	52	56	51	54
30 x 60	44	47	42	45
60 x 30	54	58	53	57
60 x 60	44	47	43	45

Candela

Angle	Along	45°	Across ⊥
0	3426	3426	3426
5	3415	3419	3427
10	3369	3393	3422
15	3296	3351	3407
20	3192	3288	3376
25	3057	3200	3318
30	2889	3083	3230
35	2676	2928	3062
40	2410	2674	2787
45	2098	2313	2462
50	1725	1853	2041
55	1333	1443	1584
60	1019	1065	1171
65	765	727	813
70	550	475	578
75	400	353	429
80	280	290	307
85	146	165	162
90	0	0	0

ORDERING INFORMATION

SAMPLE NUMBER: 2M-432A-120V-EB81-U

<p>Width 2=2' Width, 1' Width (3 Lamp)</p>	<p>Number of Lamps⁽³⁾ 2=2 Lamps 3=3 Lamps 4=4 Lamps (Not Included)</p>	<p>Voltage⁽⁴⁾ 120=120V 277=277V 347=347V UNV=Universal Voltage 120-277V⁽⁵⁾</p>	<p>Ballast Type EB8_=T8 Electronic Start. Total Harmonic Distortion < 10% EB8_/PLUS_=T8 Electronic Start. Total Harmonic Distortion < 10%. High Ballast Factor > 1.15. ER8_=T8 Electronic Program Rapid Start. Total Harmonic Distortion < 10% High Performance T8 Ballasts HB8_=T8 Electronic Instant Start. Total Harmonic Distortion < 10%. Standard Ballast Factor .86 - .88 HB8_L_=T8 Electronic Instant Start. Total Harmonic Distortion < 10%. Low Ballast Factor .77 - .82 HB8_N_=T8 Electronic Instant Start. Total Harmonic Distortion < 10%. Normal Ballast Factor 1.0 HB8_H_=T8 Electronic Instant Start. Total Harmonic Distortion < 10%. High Ballast Factor 1.15 - 1.20 HR8_=T8 Electronic Program Rapid Start. Total Harmonic Distortion < 10%. Standard Ballast Factor .86 - .88 HR8_DIM_=T8 Electronic Program Rapid Start. Total Harmonic Distortion < 10%. Step Dimming. Ballast Factor .88 HR8_L_=T8 Electronic Program Rapid Start. Total Harmonic Distortion < 10%. Low Ballast Factor .71 - .79 HR8_H_=T8 Electronic Program Rapid Start. Total Harmonic Distortion < 10%. High Ballast Factor 1.15 - 1.20</p>	<p>Options GL=Single Element Fuse GM=Double Element Fuse Emergency=Emergency Installed</p>	<p>Options VRS=Vandal Resistant⁽⁶⁾ EKO=End Plate with 7/8" KO (Required for Continuous Row Mounting)⁽⁷⁾</p>						
<p>Series^{(1), (2)} M=Modular Surface Mount</p>	<p>Wattage (Length) 32=32WT8 (48")</p>	<p>Lens A=#12 Pattern Acrylic (Standard) A125=#12 Pattern Acrylic (.125" Thick) A19/156=#19 Pattern Acrylic (.156" Thick) PB1S=Silver Parabolic Louver</p>	<p>Door Frame Standard=Flat White Steel Door (Leave Blank) FA=Flush White Extruded Aluminum c/w Spring Latch RA=Regressed White Extruded Aluminum FAN=Flush Natural Anodized Extruded Aluminum RAN=Regressed Natural Anodized Extruded Aluminum FAB=Flush Black Extruded Aluminum RAB=Regressed Black Extruded Aluminum</p>	<p>Options U=Unit Pack</p>	<p>ACCESSORIES (Order Separately) SCF=Fixed Stem Set (Specify Length) SCS=Swivel Stem Set (Specify Length) SCA=Adjustable 48" Stem Set (Additional Accessories Available. See Options and Accessories Section.)</p>						
<p>NOTES: ⁽¹⁾2' x 2', 2' x 4' require 4-point suspension, side mounted ballast recommended. ⁽²⁾Full seam welded corners on 1' x 4', 2' x 2', 2' x 4' fixtures. ⁽³⁾1' x 4', 2' x 4' 3-lamp, 2' x 4' 3-lamp have side mounted ballasts covers. ⁽⁴⁾Products also available in non-US voltages and frequencies for international markets. ⁽⁵⁾Not available when specifying emergencies, voltage must be specific. ⁽⁶⁾Available on flat doors only. ⁽⁷⁾For continuous row mounting 7/8" KOs furnished in end of fixture, specify EKO.</p>			<p>SHIPPING DATA</p> <table border="1"> <thead> <tr> <th>Catalog No.</th> <th>Wt.</th> </tr> </thead> <tbody> <tr> <td>2M-232A</td> <td>32 lbs.</td> </tr> <tr> <td>2M-432A</td> <td>36 lbs.</td> </tr> </tbody> </table>			Catalog No.	Wt.	2M-232A	32 lbs.	2M-432A	36 lbs.
Catalog No.	Wt.										
2M-232A	32 lbs.										
2M-432A	36 lbs.										

Specifications & dimensions subject to change without notice. Consult your Cooper Lighting Representative for availability and ordering information.